

nVent CADDY Speed Link SLC with Hook

The nVent CADDY Speed Link SLC with Hook delivers a fast, dependable way to suspend duct from building structures or hanging services, helping crews move quickly and reduce time on elevated surfaces. Offered in three cable lengths to cover a wide range of applications, the Speed Link SLC with Hook helps reduce on-site measuring and rework by giving installers a ready-to-use solution. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.

FEATURES

Includes wire and is assembled to a hook end fitting

Quickly and easily attaches to hanging services and building structures

Hooks to a wide range of nVent CADDY fasteners

Fastens to the building structure or hanging services by looping around and hooking to wire rope

Easy to remove for applications requiring maintenance

Spring latch helps provide a secure connection

Compatible with nVent CADDY Speed Link SLS Locking Device and nVent CADDY SLK Locking Device in 2mm and 3mm sizes (sold separately)

Material:	Steel
Finish:	Electrogalvanized
Static Load Safety Factor:	5:1
Complies With:	SMACNA HVAC-DCS

SPECIFICATIONS

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	C	Static Load
SLC2L10N	2 mm	10m	57 mm	22 mm	5.5 mm	440N
SLC2L3N	2 mm	3m	57 mm	22 mm	5.5 mm	440N
SLC2L5N	2 mm	5m	57 mm	22 mm	5.5 mm	440N
SLC3L10N	3 mm	10m	57.6 mm	23.2 mm	6.1 mm	890N
SLC3L3N	3 mm	3m	57.6 mm	23.2 mm	6.1 mm	890N

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	C	Static Load
SLC3L5N	3 mm	5m	57.6 mm	23.2 mm	6.1 mm	890N
SLC15L10N	1.5 mm	10m	48 mm	18 mm	4.5 mm	195N
SLC15L3N	1.5 mm	3m	48 mm	18 mm	4.5 mm	195N
SLC15L5N	1.5 mm	5m	48 mm	18 mm	4.5 mm	195N

Height (H): 55 mm
Width (W): 19 mm

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

