

nVent CADDY Speed Link SLC with Shot-Fire Bracket



The nVent CADDY Speed Link SLC Shot-Fire Bracket delivers a fast, dependable way to suspend duct from concrete or composite metal decking, helping crews move quickly and reduce time on elevated surfaces. Offered in three cable lengths to cover a wide range of applications, the Speed Link SLC Shot-Fire Bracket helps reduce on-site measuring and rework by giving installers a ready-to-use solution. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.

FEATURES

Includes wire and is assembled to a shot-fire bracket end fitting

Quickly and easily attaches to concrete or composite metal decking

Integrated pin installs easily using powder-actuated or single-shot gas-actuated tools

ICC-ES ESR-2024 evaluation report available for drive pin from DEWALT®

Compatible with the nVent CADDY Speed Link SLS Locking Device and nVent CADDY SLK Locking Device in 2mm and 3mm sizes (sold separately)

Material:	Steel
Finish:	Electrogalvanized
Static Load Safety Factor:	5:1
Complies With:	SMACNA HVAC-DCS

SPECIFICATIONS

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	C	Static Load
SLC2L10SF	2 mm	10m	37.5 mm	7.6 mm	31.8 mm	440N
SLC2L5SF	2 mm	5m	37.5 mm	7.6 mm	31.8 mm	440N
SLC2L3SF	2 mm	3m	37.5 mm	7.6 mm	31.8 mm	440N

Catalog Number	Wire Rope Diameter	Wire Rope Length	A	B	C	Static Load
SLC15L10SF	1.5 mm	10m	37.5 mm	7.6 mm	31.8 mm	195N
SLC15L3SF	1.5 mm	3m	37.5 mm	7.6 mm	31.8 mm	195N
SLC15L5SF	1.5 mm	5m	37.5 mm	7.6 mm	31.8 mm	195N

Angle: 90 ° Max

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

