

nVent CADDY Speed Link SLC with Y-Toggle

The nVent CADDY Speed Link SLC with Y-Toggle delivers a fast, dependable way to suspend duct from a variety of structures and hanging devices, helping crews move quickly and reduce time on elevated surfaces. Offered in three cable lengths to cover a wide range of applications, the Speed Link SLC with Y-Toggle helps reduce on-site measuring and rework by giving installers a ready-to-use solution. The tool-free locking device design makes adjustment simple and flexible when working with unknown structures or changing field conditions. Leveling and final positioning can be done quickly without specialized tools, ensuring contractors spend less time installing and more time finishing the job.

FEATURES

Includes wire and is assembled to a Y-Toggle end fitting

Quickly and easily attaches to structures and hanging devices

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

Compatible with nVent CADDY Speed Link SLS Locking Device and nVent CADDY SLK Locking Device in 2mm and 3mm sizes (sold separately)

Material:	Steel
Finish:	Electrogalvanized
Static Load Safety Factor:	5:1
Complies With:	SMACNA HVAC-DCS
Wire Rope Diameter:	1.5 mm

SPECIFICATIONS

Catalog Number	Wire Rope "Y" Length (YL)	Wire Rope Length	A	B	Static Load 1 (F1)
SLC15Y300L3N	0.3m	3m	39 mm	5 mm	195N
SLC15Y300L3R2	0.3m	3m	39 mm	5 mm	195N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

