

nVent CADDY Speed Link SLK Spool Kit



FEATURES

Kit includes spool of nVent CADDY Speed Link steel wire and nVent CADDY Speed Link SLK locking devices

Wire spool and locking devices are packaged together, simplifying transportation to the jobsite and reducing inventory

Packaging allows end-users to pull and cut any length of wire that is needed without having to take the spool out of the box

Ideal for rework and installations where custom lengths of wire may be needed

Wire rope constructed from seven bundles of seven strands each of steel aircraft wire

Push/pull keyless release allows easy adjustments

Low-profile locking device minimizes visual impact

Cable spread of 90 degrees allows positioning the device closer to the load

Keyless release tubes are easy to operate while wearing gloves

Double-sided locking mechanism enables simple height adjustment

Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Catalog Number	Wire Rope Diameter	Length	Number of Locking Devices
SLK15L500PACK	1.5 mm	150m	100

Catalog Number	Wire Rope Diameter	Length	Number of Locking Devices
SLK15L50MPACK	1.5 mm	50m	25
SLK2L100PACK	2 mm	100m	50

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

