

SK Single Piece Strut Clamp for Conduit



FEATURES

One piece break apart strut clamp for EMT and Rigid conduit

Includes thread impression and captured screw



SPECIFICATIONS

Catalog Number	Material	Finish	Outer Diameter (OD)	Width (W)	Static Load	Certifications
SK125I	Steel	Electrogalvanized	23.4 - 26.7 mm	32 mm	890N	cUL, UL
SK12ALA	Aluminum		23.4 - 26.7 mm	31.8 mm	667N	
SK165I	Steel	Electrogalvanized	29.5 - 33.4 mm	32 mm	890N	cUL, UL
SK16ALA	Aluminum		29.5 - 33.5 mm	31.8 mm	667N	
SK205I	Steel	Electrogalvanized	38.4 - 42.2 mm	32 mm	890N	cUL, UL
SK20ALA	Aluminum		38.4 - 42.2 mm	31.8 mm	667N	
SK245I	Steel	Electrogalvanized	44.2 - 48.3 mm	32 mm	890N	cUL, UL
SK24ALA	Aluminum		44.2 - 48.3 mm	31.8 mm	667N	
SK325I	Steel	Electrogalvanized	55.8 - 60.3 mm	32 mm	890N	cUL, UL
SK32ALA	Aluminum		55.9 - 60.5 mm	31.8 mm	667N	
SK405I	Steel	Electrogalvanized	73 mm	32 mm	1560N	cUL, UL
SK485I	Steel	Electrogalvanized	88.9 mm	32 mm	1560N	cUL, UL
SK565I	Steel	Electrogalvanized	101.6 mm	32 mm	1560N	cUL, UL

Catalog Number	Material	Finish	Outer Diameter (OD)	Width (W)	Static Load	Certifications
SK645I	Steel	Electrogalvanized	114.3 mm	32 mm	1560N	cUL, UL
SK85I	Steel	Electrogalvanized	17.9 - 21.3 mm	32 mm	890N	UL, cUL
SK8ALA	Aluminum		18.0 - 21.3 mm	31.8 mm	667N	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical
 Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

