

Threaded Stud


FEATURES

Pre-cut lengths of threaded rod



SPECIFICATIONS

Catalog Number	Material	Finish	Tensile Strength	Yield Strength	Rod Size (RS)	Length (L)	Static Load
0513702PL	Steel	Plain	400 MPa	248211kPa	3/8"	50.8mm	2700N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

