

VF Series C Purlin Clip



FEATURES

Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from purlin and bar joist

Installs from floor with VAFT tool and conduit




SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Flange Thickness (FT)	A	B	C
VF14	Spring Steel	nVent CADDY Armour	1.5 - 6 mm	20 mm Min	80 mm	90 mm

Table 2/2

Catalog Number	Hole Size (HS)	Static Load
VF14	7.1 mm	700N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

