


Wire Basket Tray Polymer Insert



The nVent CADDY Wire Basket Tray Polymer Insert utilizes a flame-retardant polymer to envelop the entire tray- providing bottom, side and cover protection. Available options include a flat bottom or a prescored version to the tray depth for coverage of the bottom and sides.

FEATURES

Standard black finish for use with divider posts

Polymer insert rolls into the tray bottom

Multiple color options to coordinate with cable tray selection

Color: Black
Material: Polymer

SPECIFICATIONS

Table 1/2


Catalog Number	Height (H)	Width (W)	Length (L)	Sides Included	Unit Weight
WBTFORM04BA		92.2 mm	3048mm	No	0.02 kg
WBTFORM06BA		143 mm	3048mm	No	0.03 kg
WBTFORM08BA		193.8 mm	3048mm	No	0.04 kg
WBTFORM12BA		295.4 mm	3048mm	No	0.06 kg
WBTFORM16BA		397 mm	3048mm	No	0.08 kg
WBTFORM18BA		447.8 mm	3048mm	No	0.09 kg
WBTFORM20BA		498.6 mm	3048mm	No	0.1 kg
WBTFORM24BA		600.2 mm	3048mm	No	0.12 kg
WBTFORM2X12BA	50.8 mm	295.4 mm	3048mm	Yes	0.08 kg
WBTFORM2X16BA	50.8 mm	397 mm	3048mm	Yes	0.1 kg
WBTFORM2X18BA	50.8 mm	447.8 mm	3048mm	Yes	0.11 kg
WBTFORM2X20BA	50.8 mm	498.6 mm	3048mm	Yes	0.12 kg
WBTFORM2X24BA	50.8 mm	600.2 mm	3048mm	Yes	0.14 kg
WBTFORM2X4BA	50.8 mm	92.2 mm	3048mm	Yes	0.04 kg
WBTFORM2X6BA	50.8 mm	143 mm	3048mm	Yes	0.05 kg

Catalog Number	Height (H)	Width (W)	Length (L)	Sides Included	Unit Weight
WBTFORM2X8BA	50.8 mm	193.8 mm	3048mm	Yes	0.06 kg
WBTFORM4X12BA	101.6 mm	295.4 mm	3048mm	Yes	0.1 kg
WBTFORM4X16BA	101.6 mm	397 mm	3048mm	Yes	0.12 kg
WBTFORM4X18BA	101.6 mm	447.8 mm	3048mm	Yes	0.13 kg
WBTFORM4X20BA	101.6 mm	498.6 mm	3048mm	Yes	0.14 kg

Table 2/2

Catalog Number	Height (H)	Width (W)	Length (L)	Sides Included	Unit Weight
WBTFORM4X24BA	101.6 mm	600.2 mm	3048mm	Yes	0.16 kg
WBTFORM4X4BA	101.6 mm	92.2 mm	3048mm	Yes	0.06 kg
WBTFORM4X6BA	101.6 mm	143 mm	3048mm	Yes	0.07 kg
WBTFORM4X8BA	101.6 mm	193.8 mm	3048mm	Yes	0.08 kg
WBTFORM6X12BA	152.4 mm	295.4 mm	3048mm	Yes	0.12 kg
WBTFORM6X16BA	152.4 mm	397 mm	3048mm	Yes	0.14 kg
WBTFORM6X18BA	152.4 mm	447.8 mm	3048mm	Yes	0.16 kg
WBTFORM6X20BA	152.4 mm	498.6 mm	3048mm	Yes	0.18 kg
WBTFORM6X24BA	152.4 mm	600.2 mm	3048mm	Yes	0.18 kg
WBTFORM6X8BA	152.4 mm	193.8 mm	3048mm	Yes	0.1 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

