


Wire Basket Tray PreForm Elbow 90°



The nVent CADDY Wire Basket Tray PreForm Elbow 90° is a precision-engineered solution designed to streamline cable tray installations when a directional change is needed. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Elbow 90° delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Elbow 90° significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

FEATURES

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in multiple directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Material: Steel
Finish: Pregalvanized; Polyurethane



SPECIFICATIONS

Table 1/2

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTR902X12		50.8 mm	515.62 mm	515.62mm	19.05 mm	94.64mm
WBTR902X12BA	Black	50.8 mm	515.62 mm	515.62mm	19.05 mm	94.64mm
WBTR902X12WH	White	50.8 mm	515.62 mm	515.62mm	19.05 mm	94.64mm
WBTR902X16		50.8 mm	617.22 mm	617.22mm	19.05 mm	94.64mm
WBTR902X16WH	White	50.8 mm	617.22 mm	617.22mm	19.05 mm	94.64mm
WBTR902X18		50.8 mm	665.734 mm	665.734mm	19.05 mm	94.64mm
WBTR902X18BA	Black	50.8 mm	665.734 mm	665.734mm	19.05 mm	94.64mm
WBTR902X18WH	White	50.8 mm	665.734 mm	665.734mm	19.05 mm	94.64mm

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTR902X20BA	Black	50.8 mm	716.28 mm	716.28mm	19.05 mm	94.64mm
WBTR902X24		50.8 mm	817.88 mm	817.88mm	19.05 mm	94.64mm
WBTR902X24BA	Black	50.8 mm	817.88 mm	817.88mm	19.05 mm	94.64mm
WBTR902X24WH	White	50.8 mm	817.88 mm	817.88mm	19.05 mm	94.64mm
WBTR902X4		50.8 mm	317.7 mm	317.7mm		94.64mm
WBTR902X4BA	Black	50.8 mm	317.7 mm	317.7mm		94.64mm
WBTR902X4WH	White	50.8 mm	317.7 mm	317.7mm		94.64mm
WBTR902X6		50.8 mm	365.76 mm	365.76mm		94.64mm
WBTR902X6BA	Black	50.8 mm	365.76 mm	365.76mm		94.64mm
WBTR902X6WH	White	50.8 mm	365.76 mm	365.76mm		94.64mm
WBTR902X8		50.8 mm	416.56 mm	416.56mm		94.64mm
WBTR902X8BA	Black	50.8 mm	416.56 mm	416.56mm		94.64mm

Table 2/2

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)
WBTR902X8WH	White	50.8 mm	416.56 mm	416.56mm		94.64mm

Table 1/2


Catalog Number	Unit Weight	Certifications
WBTR902X12	1.814 kg	cUL, UL, CE, nVent CADDY Wire Basket Tray System
WBTR902X12BA	1.814 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X12WH	1.814 kg	
WBTR902X16	2.722 kg	UL, cUL
WBTR902X16WH	2.722 kg	
WBTR902X18	3.175 kg	CE, nVent CADDY Wire Basket Tray System, cUL, UL
WBTR902X18BA	3.175 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X18WH	3.175 kg	
WBTR902X20BA	4.082 kg	
WBTR902X24	4.99 kg	cUL, UL, CE, nVent CADDY Wire Basket Tray System
WBTR902X24BA	4.99 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X24WH	4.99 kg	
WBTR902X4	0.454 kg	UL, CE, nVent CADDY Wire Basket Tray System, cUL
WBTR902X4BA	0.454 kg	CE, nVent CADDY Wire Basket Tray System
WBTR902X4WH	0.454 kg	
WBTR902X6	0.907 kg	CE, nVent CADDY Wire Basket Tray System, cUL, UL
WBTR902X6BA	0.907 kg	CE, nVent CADDY Wire Basket Tray System

Catalog Number	Unit Weight	Certifications
WBTR902X6WH	0.907 kg	
WBTR902X8	0.907 kg	UL, cUL, CE, nVent CADDY Wire Basket Tray System
WBTR902X8BA	0.907 kg	CE, nVent CADDY Wire Basket Tray System

Table 2/2

Catalog Number	Unit Weight	Certifications
WBTR902X8WH	0.907 kg	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

