

# Wire Basket Tray PreForm Tee



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## FEATURES

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Material:** Steel  
**Finish:** Pregalvanized; Polyurethane



## SPECIFICATIONS

Table 1/2

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Radius (R) |
|----------------|-------|------------|-----------|------------|----------------|------------|
| WBTT2X12       |       | 50.8 mm    | 515.62 mm | 711.2mm    | 19.05 mm       | 94.64mm    |
| WBTT2X12BA     | Black | 50.8 mm    | 515.62 mm | 711.2mm    | 19.05 mm       | 94.64mm    |
| WBTT2X12WH     | White | 50.8 mm    | 515.62 mm | 711.2mm    | 19.05 mm       | 94.64mm    |
| WBTT2X16       |       | 50.8 mm    | 617.22 mm | 812.8mm    | 19.05 mm       | 94.64mm    |
| WBTT2X16BA     | Black | 50.8 mm    | 617.22 mm | 812.8mm    | 19.05 mm       | 94.64mm    |
| WBTT2X16WH     | White | 50.8 mm    | 617.22 mm | 812.8mm    | 19.05 mm       | 94.64mm    |
| WBTT2X18       |       | 50.8 mm    | 668.02 mm | 863.6mm    | 19.05 mm       | 94.64mm    |

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Radius (R) |
|----------------|-------|------------|-----------|------------|----------------|------------|
| WBTT2X18BA     | Black | 50.8 mm    | 668.02 mm | 863.6mm    | 19.05 mm       | 94.64mm    |
| WBTT2X18WH     | White | 50.8 mm    | 668.02 mm | 863.6mm    | 19.05 mm       | 94.64mm    |
| WBTT2X20BA     | Black | 50.8 mm    | 716.28 mm | 911.86mm   | 19.05 mm       | 94.64mm    |
| WBTT2X20WH     | White | 50.8 mm    | 716.28 mm | 911.86mm   | 19.05 mm       | 94.64mm    |
| WBTT2X24       |       | 50.8 mm    | 817.88 mm | 1013.46mm  | 19.05 mm       | 94.64mm    |
| WBTT2X24BA     | Black | 50.8 mm    | 817.88 mm | 1013.46mm  | 19.05 mm       | 94.64mm    |
| WBTT2X24WH     | White | 50.8 mm    | 817.88 mm | 1013.46mm  | 19.05 mm       | 94.64mm    |
| WBTT2X4        |       | 50.8 mm    | 317.5 mm  | 513.08mm   |                | 94.64mm    |
| WBTT2X4BA      | Black | 50.8 mm    | 317.5 mm  | 513.08mm   |                | 94.64mm    |
| WBTT2X4WH      | White | 50.8 mm    | 317.5 mm  | 513.08mm   |                | 94.64mm    |
| WBTT2X6        |       | 50.8 mm    | 365.76 mm | 561.34mm   |                | 94.64mm    |
| WBTT2X6BA      | Black | 50.8 mm    | 365.76 mm | 561.34mm   |                | 94.64mm    |
| WBTT2X6WH      | White | 50.8 mm    | 365.76 mm | 561.34mm   |                | 94.64mm    |

Table 2/2

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Radius (R) |
|----------------|-------|------------|-----------|------------|----------------|------------|
| WBTT2X8        |       | 50.8 mm    | 416.56 mm | 612.14mm   |                | 94.64mm    |
| WBTT2X8BA      | Black | 50.8 mm    | 416.56 mm | 612.14mm   |                | 94.64mm    |
| WBTT2X8WH      | White | 50.8 mm    | 416.56 mm | 612.14mm   |                | 94.64mm    |

Table 1/2

| Catalog Number | Unit Weight | Certifications                          |
|----------------|-------------|-----------------------------------------|
| WBTT2X12       | 2.722 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X12BA     | 2.722 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X12WH     | 2.722 kg    |                                         |
| WBTT2X16       | 3.629 kg    |                                         |
| WBTT2X16BA     | 3.629 kg    |                                         |
| WBTT2X16WH     | 3.629 kg    |                                         |
| WBTT2X18       | 4.536 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X18BA     | 4.536 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X18WH     | 4.536 kg    |                                         |
| WBTT2X20BA     | 5.897 kg    |                                         |
| WBTT2X20WH     | 5.897 kg    |                                         |
| WBTT2X24       | 7.257 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X24BA     | 7.257 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X24WH     | 7.257 kg    |                                         |

| Catalog Number | Unit Weight | Certifications                          |
|----------------|-------------|-----------------------------------------|
| WBTT2X4        | 0.454 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X4BA      | 0.454 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X4WH      | 0.454 kg    |                                         |
| WBTT2X6        | 1.361 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X6BA      | 1.361 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X6WH      | 1.361 kg    |                                         |

Table 2/2

| Catalog Number | Unit Weight | Certifications                          |
|----------------|-------------|-----------------------------------------|
| WBTT2X8        | 1.814 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X8BA      | 1.814 kg    | CE, nVent CADDY Wire Basket Tray System |
| WBTT2X8WH      | 1.814 kg    |                                         |

## DIAGRAMS

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

