

ABP Perforated Strap with Rounded Edge, Standard Duty

FEATURES

Steel perforated mounting strap

Enclosed in plastic case



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Width	Length	Thickness
ABP12PG	583920	Steel	Pregalvanized	12 mm	10m	0.8 mm
ABP12S4	584020	Stainless Steel 304 (EN 1.4301)		12 mm	10m	0.8 mm
ABP17PG	583930	Steel	Pregalvanized	17 mm	10m	0.8 mm

Table 2/2

Catalog Number	Article Number	Hole Size	Static Load
ABP12PG	583920	5 mm	560N
ABP12S4	584020	5 mm	700N
ABP17PG	583930	7 mm	800N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDD1](https://www.nvent.com/ENDD1)

