


# Front/Rear Bottom Frames For Floor Standing Enclosures, PCU



This frame creates additional space in the bottom and can be segregated from the enclosure. It has a universal hole pattern for mounting accessories easily.

## FEATURES

**Description:** For fixing and routing of cables or mounting of busbar. Identical hole pattern to the enclosure's frame makes all relevant accessories (e.g. CLPF, CLPK, etc) possible to mount. Fixed to the base of the enclosure by M12 screws (provided).

**Side panels:** PCUP supplied as an accessory.

**Material:** Frame in 1.75 mm steel plate, panels in 1.35 mm steel plate.

**Finish:** RAL 7035 structured powder coating.

**Protection:** Complies with IP 55.

**Pack quantity:** 1 piece with front and back panels including mounting accessories. Add CBP for closing bottom opening.

**Material:** Steel  
**Finish:** Plated  
**Color:** Light Gray  
**Color Code:** RAL 7035

## SPECIFICATIONS

| Catalog Number | Height | Width | Depth | Enclosure Material |
|----------------|--------|-------|-------|--------------------|
| PCU3046R5      | 300mm  | 400mm | 600mm | Stainless Steel    |

| Catalog Number | Height | Width  | Depth | Enclosure Material |
|----------------|--------|--------|-------|--------------------|
| PCU3048R5      | 300mm  | 400mm  | 800mm | Stainless Steel    |
| PCU3066R5      | 300mm  | 599mm  | 600mm | Stainless Steel    |
| PCU3068R5      | 300mm  | 599mm  | 800mm | Stainless Steel    |
| PCU3086R5      | 300mm  | 800mm  | 600mm | Stainless Steel    |
| PCU3088R5      | 300mm  | 800mm  | 800mm | Stainless Steel    |
| PCU3106R5      | 300mm  | 999mm  | 600mm | Stainless Steel    |
| PCU3108R5      | 300mm  | 999mm  | 800mm | Stainless Steel    |
| PCU3126R5      | 300mm  | 1199mm | 600mm | Stainless Steel    |
| PCU3128R5      | 300mm  | 1199mm | 800mm | Stainless Steel    |
| PCU2046R5      | 200mm  | 400mm  | 600mm | Stainless Steel    |
| PCU2048R5      | 200mm  | 400mm  | 800mm | Stainless Steel    |
| PCU2066R5      | 200mm  | 599mm  | 600mm | Stainless Steel    |
| PCU2068R5      | 200mm  | 599mm  | 800mm | Stainless Steel    |
| PCU2086R5      | 200mm  | 800mm  | 600mm | Stainless Steel    |
| PCU2088R5      | 200mm  | 800mm  | 800mm | Stainless Steel    |
| PCU2106R5      | 200mm  | 999mm  | 600mm | Stainless Steel    |
| PCU2108R5      | 200mm  | 999mm  | 800mm | Stainless Steel    |
| PCU2126R5      | 200mm  | 1199mm | 600mm | Stainless Steel    |
| PCU2128R5      | 200mm  | 1199mm | 800mm | Stainless Steel    |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.