

H-MSM Conduit/Pipe to Flange Clip, Side Mount



FEATURES

Supports conduit/pipe or cable from beam flanges

Snap close clip pivots a full 360°

Requires only a hammer to install

Material: Spring Steel
Finish: nVent CADDY Armour




SPECIFICATIONS

Catalog Number	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	Static Load	Certifications
16M24SM	173720	23.4 - 35 mm	3 - 8 mm	120N	UL, cUL
16M58SM	173730	23.4 - 35 mm	8 - 14 mm	120N	cUL, UL
16M912SM	173740	23.4 - 35 mm	14 - 20 mm	120N	cUL, UL
20M24SM	171720	35 - 42 mm	3 - 8 mm	120N	UL, cUL
20M58SM	173770	35 - 42 mm	8 - 14 mm	120N	
20M912SM	173780	35 - 42 mm	14 - 20 mm	120N	
24M24SM	176690	42 - 50 mm	3 - 8 mm	120N	UL, cUL
24M58SM	173800	42 - 50 mm	8 - 14 mm	120N	UL, cUL
24M912SM	173810	42 - 50 mm	14 - 20 mm	120N	UL, cUL
32M24SM	173830	50 - 60 mm	3 - 8 mm	120N	cUL, UL
32M58SM	173840	50 - 60 mm	8 - 14 mm	120N	cUL, UL
32M912SM	173850	50 - 60 mm	14 - 20 mm	120N	UL, cUL
812M24SM	160050	18 - 30 mm	3 - 8 mm	120N	ITB, cUL, UL

Catalog Number	Article Number	Outer Diameter (OD)	Flange Thickness (FT)	Static Load	Certifications
812M58SM	160060	18 - 30 mm	8 - 14 mm	120N	cUL, ITB, UL
812M912SM	160070	18 - 30 mm	14 - 20 mm	120N	cUL, UL, ITB

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
 Option 1 – Customer Care
 Option 2 – Technical Support

Europe

Netherlands:
 +31 800-0200135
 France:
 +33 800 901 793

Europe

Germany:
 800 1890272
 Other Countries:
 +31 13 5835404

APAC

Shanghai:
 + 86 21 2412 1618/19
 Sydney:
 +61 2 9751 8500

