


# Seismic Lighting Fixture Clamp



## FEATURES

Secures fluorescent light fixtures to the ceiling frame members

Requires no additional chains, cables or slack wires attached to the fixture

Helps strengthen integrity of the T-Grid system

Holds in place against the force of standard fire-hose pressure

Meets U.S. building code and electrical code specifications

Also satisfies NEC® 410.16(C) positive attachment for secure fastening of luminaires (fixtures) complying with Building Code Reference AC184

Reusable and cost effective

**Material:** Steel

**Finish:** Plain



## SPECIFICATIONS

| Catalog Number | Article Number | Fixture Configuration                                       |
|----------------|----------------|-------------------------------------------------------------|
| SFCLT          |                | One Standard Tapered 0.61 x 1.22 m Fixture                  |
| SFCLTCF        | 402245         | One 0.61 x 0.61 m Fixture                                   |
| SFCLTCFS       |                | Reinforcement of T-Bar Main Runner/Cross Runner Connections |

| Catalog Number | Article Number | Fixture Configuration                                    |
|----------------|----------------|----------------------------------------------------------|
| SFCLTE         |                | Two Standard Tapered 0.61 x 1.22 m Fixtures Side-by-Side |
| SFCLTS         |                | Two Standard Tapered 0.61 x 1.22 m Fixtures Side-by-Side |

ADDITIONAL PRODUCT DETAILS

Tested for compliance to the UBC, NEC®, NBC, and CEC.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

