

# Threaded Bridle Ring



## FEATURES

Combine bridle rings with other nVent CADDY fasteners to support cables from flange, purlin, drop wire, t-grid, etc.

**Material:** Steel  
**Finish:** Electrogalvanized



## SPECIFICATIONS

| Catalog Number | Article Number | Diameter | Screw Diameter | Screw Type | Screw Length | Ultimate Static Load | Certifications |
|----------------|----------------|----------|----------------|------------|--------------|----------------------|----------------|
| 2BRT12         |                | 19.1 mm  | 4.8            | Metal      | 14.3mm       | 220N                 | UL, cUL        |
| 2BRT20         |                | 31.8 mm  | 4.8            | Metal      | 14.3mm       | 220N                 | UL, cUL        |
| 2BRT32         |                | 50.8 mm  | 4.8            | Metal      | 14.3mm       | 220N                 | cUL, UL        |
| 2BRT8          |                | 12.7 mm  | 4.8            | Metal      | 14.3mm       | 220N                 | UL, cUL        |
| 4BRT20         |                | 31.8 mm  | 6              | Metal      | 19mm         | 220N                 | UL, cUL        |
| 4BRT20WS       |                | 31.8 mm  | 14             | Wood       | 19.1mm       | 220N                 | UL, cUL        |
| 4BRT32         |                | 50 mm    | 6              | Metal      | 19mm         | 220N                 | cUL, UL        |
| 4BRT32WS       | 172923         | 50 mm    | 14             | Wood       | 19mm         | 220N                 | cUL, ITB, UL   |
| 4BRT64         |                | 100 mm   | 6              | Metal      | 19mm         | 220N                 | cUL, UL        |

## ADDITIONAL PRODUCT DETAILS

Bridle Rings not recommended for high performance cables. See nVent CADDY Cat HP J-Hook System.

**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

