

VF-Ti/T Rod to C-Purlin Clip



FEATURES

Hammer-on or install from the floor with the VAFT tool



Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from purlin and bar joist

Material: Spring Steel
Finish: nVent CADDY Armour



SPECIFICATIONS

Catalog Number	Hole Size (HS)	Hole Type	Flange Thickness (FT)	Height (H)	Static Load
VF144TI	0.25 mm	Threaded	1.5 - 6 mm	132 mm	700N
VF146T	9.5 mm	Plain	1.5 - 6 mm	132 mm	700N
VF146TI	0.375 mm	Threaded	1.5 - 6 mm	132 mm	700N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

