


Portable Rail Grinder Slotting Wheel Kit

FEATURES

Used with SBG150 Portable Rail Grinder, Two-Cycle Gas-Powered

Quick and easy installation

Enables control of slotting operations, aiding the insulated rail joint (IRJ) maintenance operation



Material: Reinforced Resinoid-Bonded Aluminum Oxide

SPECIFICATIONS

Catalog Number	Diameter	Thickness
SBK104	152.4 mm	3.18 mm
SBK128	152.4 mm	3.97 mm

ADDITIONAL PRODUCT DETAILS

Kit includes: slotting wheel, spacer, depth gauge, and insulation.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

