

VF-Ti/T Rod to C-Purlin Clip, Spring Steel, 6.4 mm Hole, Threaded, 1.5–6 mm Flange



CATALOG NUMBER

VF144TI

FEATURES

Hammer-on or install from the floor with the VAFT tool

Provides an attachment for nVent CADDY Speed Link assemblies, wire, S-hooks, or chain from purlin and bar joist



PRODUCT ATTRIBUTES

Material: Spring Steel

Finish: nVent CADDY Armour



Hole Size (HS): 0.25 mm

Hole Type: Threaded

Flange Thickness (FT): 1.5 - 6 mm

Height (H): 132 mm

Static Load: 700N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

