

Strut Beam Clamp with U-Bolt



FEATURES

Complete with U-bolt and nuts

Requires installation in pairs

Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Table 1/2


Catalog Number	Strut Type	Rod Size (RS)	Flange Thickness (FT)	Width (W)	Thickness (T)	A
BC17A000EG	A (41 x 41 mm), C (21 x 41 mm)	0.375	20.6 mm Max	76.2 mm	6.35 mm	26.99 mm
BC17D000EG	AA (83 x 41 mm), D (62 x 41 mm), E (83 x 41 mm)	0.375	20.6 mm Max	76.2 mm	6.35 mm	26.99 mm

Table 2/2

Catalog Number	B	C	Static Load
BC17A000EG	42.86 mm	85.72 mm	5300N
BC17D000EG	42.86 mm	127 mm	5300N

ADDITIONAL PRODUCT DETAILS

Static Load is based on one pair of Strut Beam Clamps.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

