

C-EC Cable to Strut Clamp



FEATURES

One-piece cable/conduit clamp with protective boot

No screws or bolts to drop

Requires only a screwdriver or nutdriver for installation

Fits into open side of strut channel

Material: Steel
Finish: Hot-Dip Galvanized

SPECIFICATIONS




Catalog Number	Article Number	Outer Diameter (OD)	Width (W)	Thickness (T)	Torque (TQ)	A	B
C12EC	337600	8 - 12 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C16EC	337610	12 - 16 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C20EC	337620	16 - 20 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C24EC	337630	20 - 24 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C28EC	337640	24 - 28 mm	20 mm	1.5 mm	2 N·m	18 mm Min	10 mm Max
C32EC	337650	28 - 32 mm	25 mm	1.75 mm	2 N·m	18 mm Min	10 mm Max
C36EC	337660	32 - 36 mm	25 mm	1.75 mm	2 N·m	18 mm Min	10 mm Max

Catalog Number	ArticleNumber	Outer Diameter (OD)	Width(W)	Thickness(T)	Torque(TQ)	A	B
C40EC	337670	36 - 40 mm	25 mm	1.75 mm	2 N·m	18 mm Min	10 mm Max
C44EC	337680	40 - 44 mm	25 mm	2 mm	4 N·m	18 mm Min	10 mm Max
C48EC	337690	44 - 48 mm	25 mm	2 mm	4 N·m	18 mm Min	10 mm Max
C52EC	337700	48 - 52 mm	25 mm	2 mm	4 N·m	18 mm Min	10 mm Max
C56EC	337710	52 - 56 mm	25 mm	2 mm	4 N·m	18 mm Min	10 mm Max
C60EC	337720	56 - 60 mm	30 mm	2.25 mm	4 N·m	18 mm Min	10 mm Max
C64EC	337730	60 - 64 mm	30 mm	2.25 mm	4 N·m	18 mm Min	10 mm Max

ADDITIONAL PRODUCT DETAILS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

