


U-Bolt

FEATURES

Complete with 4 nuts



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)	Height (H)
UB4N049M8	599160	Steel	Electrogalvanized	49 mm	40	M8	78 mm
UB4N090M10	599190	Steel	Electrogalvanized	90 mm	80	M10	125 mm
UB4N160M8	599338	Steel	Electrogalvanized	160 mm		M8	214 mm
UB4N160M8S6	599351	Stainless Steel 316 (EN 1.4401)		160 mm		M8	214 mm
UB4N219M10S6	599354	Stainless Steel 316 (EN 1.4401)		219 mm	200	M10	286 mm
UB4N219M16	599250	Steel	Electrogalvanized	219 mm	200	M16	286 mm
UB4N273M16	599260	Steel	Electrogalvanized	273 mm	250	M16	331 mm

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)	Height (H)
UB4N323M10	599343	Steel	Electrogalvanized	323 mm	300	M10	389 mm
UB4N30M6EG	599405	Steel	Electrogalvanized	30 mm	20	M6	60 mm
UB4N30M6S6	599490	Stainless Steel 316 (EN 1.4401)		30 mm	20	M6	60 mm
UB4N36M8EG	599410	Steel	Electrogalvanized	36 mm	25	M8	70 mm
UB4N36M8S6	599495	Stainless Steel 316 (EN 1.4401)		36 mm	25	M8	70 mm
UB4N46M6S6	599510	Stainless Steel 316 (EN 1.4401)		46 mm	32	M6	80 mm
UB4N52M8S6	599515	Stainless Steel 316 (EN 1.4401)		52 mm	40	M8	90 mm
UB4N64M8S6	599520	Stainless Steel 316 (EN 1.4401)		65 mm	50	M8	100 mm
UB4N74M8EG	599430	Steel	Electrogalvanized	74 mm	65	M8	120 mm
UB4N118M10EG	599445	Steel	Electrogalvanized	118 mm	100	M10	140 mm
UB4N118M10S6	599535	Stainless Steel 316 (EN 1.4401)		118 mm	100	M10	165 mm
UB4N146M12EG	599450	Steel	Electrogalvanized	146 mm	125	M12	200 mm
UB4N146M12S6	599540	Stainless Steel 316 (EN 1.4401)		146 mm	125	M12	200 mm

Table 2/2

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)	Height (H)
UB4N168M12EG	599455	Steel	Electrogalvanized	168 mm		M12	220 mm
UB4N168M12S6	599545	Stainless Steel 316 (EN 1.4401)		168 mm		M12	220 mm
UB4N172M16EG	599460	Steel	Electrogalvanized	172 mm	150	M16	240 mm
UB4N172M16S6	599550	Stainless Steel 316 (EN 1.4401)		172 mm	150	M16	240 mm
UB4N224M12S6	599555	Stainless Steel 316 (EN 1.4401)		224 mm	200	M12	295 mm

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)	Height (H)
UB4N224M16EG	599470	Steel	Electrogalvanized	224 mm	200	M16	295 mm
UB4N23M6S6	599485	Stainless Steel 316 (EN 1.4401)		23 mm	10	M6	50 mm
UB4N278M16EG	599475	Steel	Electrogalvanized	278 mm	250	M16	350 mm
UB4N278M16S6	599560	Stainless Steel 316 (EN 1.4401)		278 mm	250	M16	350 mm
UB4N329M16EG	599480	Steel	Electrogalvanized	345 mm	300	M16	400 mm
UB4N329M16S6	599565	Stainless Steel 316 (EN 1.4401)		345 mm	300	M16	400 mm
UB4N46M6EG	599415	Steel	Electrogalvanized	42 mm	32	M8	80 mm
UB4N52M8EG	599420	Steel	Electrogalvanized	49 mm	40	M8	90 mm
UB4N64M8EG	599425	Steel	Electrogalvanized	60 mm	50	M8	100 mm
UB4N74M8S6	599525	Stainless Steel 316 (EN 1.4401)		74 mm	65	M8	120 mm
UB4N94M10EG	599440	Steel	Electrogalvanized	94 mm	80	M10	140 mm
UB4N94M10S6	599530	Stainless Steel 316 (EN 1.4401)		94 mm	80	M10	140 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

