

# Wire Basket Tray Independent Underfloor Support



The nVent CADDY Wire Basket Tray Underfloor Support provides a reliable method for routing wire basket trays beneath the floor with independent structural support. This component is ideal for installations requiring low-voltage cabling to pass under cabinets or equipment.

Engineered for stability and simplicity, the underfloor support system eliminates the need for complex framing. It braces the tray directly beneath raised floors, allowing for clean, unobtrusive cable pathways that preserve floor space and reduce visual clutter. This is especially valuable in data centers, control rooms, and other high-density environments where cable organization and accessibility are critical.

The Support integrates seamlessly with the broader nVent CADDY Wire Basket Tray System, ensuring compatibility with shaped and round wire tray profiles. Its design accommodates standard fasteners and finishes, including pre-galvanized, zinc electroplate, and powder coat options, making it adaptable to a wide range of project specifications.

## FEATURES

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Maintains a fixed and secure distance from the ground to ensure safety and accessibility

Available in a range of sizes to match wire basket tray design

Fixed height ensures a level installation


**Material:** Steel  
**Finish:** Pregalvanized

## SPECIFICATIONS

| Catalog Number | Height (H) | Length (L) | Length 1 (L1) | Width (W) | Hole Size (HS) | Unit Weight |
|----------------|------------|------------|---------------|-----------|----------------|-------------|
| WBTUS04        | 32 mm      | 767mm      | 560.78 mm     | 235 mm    | 14.3 mm        | 0.862 kg    |
| WBTUS06        | 32 mm      | 868mm      | 560.78 mm     | 235 mm    | 14.3 mm        | 0.953 kg    |
| WBTUS08        | 32 mm      | 965mm      | 560.78 mm     | 235 mm    | 14.3 mm        | 1.089 kg    |
| WBTUS12        | 32 mm      | 1174mm     | 560.78 mm     | 235 mm    | 14.3 mm        | 1.588 kg    |
| WBTUS18        | 32 mm      | 1474mm     | 560.78 mm     | 235 mm    | 14.3 mm        | 2.404 kg    |

| Catalog Number | Height (H) | Length (L) | Length 1 (L1) | Width (W) | Hole Size (HS) | Unit Weight |
|----------------|------------|------------|---------------|-----------|----------------|-------------|
| WBTUS24        | 32 mm      | 1778mm     | 560.78 mm     | 235 mm    | 14.3 mm        | 3.22 kg     |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

