


6000 Beam Clamp Kit



FEATURES

Back-to-back welded channels provide a smooth and easy adjustable fixing over the complete length of the channel

Pressure clamps grip the strut channel between two lips, protecting it from turning

Safe heavy duty fixing system for cable tray, duct or pipe

Material: Steel
Finish: Hot-Dip Galvanized

SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Length (L)	Strut Type	Rod Size (RS)	Flange Thickness (FT)	A
6300CCHD	330000	300mm	CC (41 x 41 mm)	10	3 - 30 mm	26 mm
6400AAHD	330110	400mm	AA (83 x 41 mm)	10	3 - 30 mm	26 mm
6400CCHD	330010	400mm	CC (41 x 41 mm)	10	3 - 30 mm	26 mm
6500CCHD	330020	500mm	CC (41 x 41 mm)	10	3 - 30 mm	26 mm
6600AAHD	330130	600mm	AA (83 x 41 mm)	10	3 - 30 mm	26 mm
6600CCHD	330030	600mm	CC (41 x 41 mm)	10	3 - 30 mm	26 mm
6800AAHD	330140	800mm	AA (83 x 41 mm)	10	3 - 30 mm	26 mm


Table 2/2

Catalog Number	Article Number	B	Torque (TQ)
6300CCHD	330000	13 mm	30 N·m
6400AAHD	330110	13 mm	30 N·m
6400CCHD	330010	13 mm	30 N·m

Catalog Number	Article Number	B	Torque (TQ)
6500CCHD	330020	13 mm	30 N·m
6600AAHD	330130	13 mm	30 N·m
6600CCHD	330030	13 mm	30 N·m
6800AAHD	330140	13 mm	30 N·m

Strut Type	A	Static Load 1 F1	Static Load 2 F2
CC	200 mm	4000 N	1100 N
	300 mm	3000 N	750 N
	400 mm	2250 N	550 N
	500 mm	1800 N	450 N
	600 mm	1500 N	350 N
AA	200 mm	7000 N	3250 N
	300 mm	7000 N	2250 N
	400 mm	7000 N	1750 N
	500 mm	5500 N	1400 N
	600 mm	4500 N	1150 N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

