


PEMSA Wire Basket Tray Quick Center Support

FEATURES

Ideal for tray widths up to 200mm

Side load access for cable installation

IEC 61537 load rating and earthing compliant




SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Length (L)	Width (W)	Height (H)
WBTQCTRSPRTM10	820425	Steel	Electrogalvanized	59mm	35 mm	5 mm

Table 2/2

Catalog Number	Article Number	Hole Size (HS)	Static Load
WBTQCTRSPRTM10	820425	8 - 10 mm	833N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

