

Hygienic Design, Floor Standing Enclosure, HDF



The Hygienic Design Floor Standing Enclosure, HDF range, is specially engineered to protect electrical equipment in sanitary environments requiring high cleanliness, including during high pressure, high temperature washdown and clean-in-place (CIP) procedures. With self-draining, smooth-finished surfaces, gap-free design and high protection degree, the enclosure minimizes hygiene risks and helps reduce downtime to increase productivity.

INDUSTRY STANDARDS

cULus_UL
CE, UK CA, UL
IP66/69

FEATURES

Material: AISI 304L pre-grained stainless steel. Body: 1.5 mm. Frame: 1.5 mm. Door: 2 mm. Mounting plate: 3 mm galvanized steel

30-degree front-sloped top prevents fluids and particulates from pooling or accumulating. Integrated vertical and depth profiles with hole pattern allow adjustment of mounting plate. Rivet nuts on bottom allow mounting of leveling feet, available as accessory

Folded with an 8-degree sloped angle on all sides. Opening 120 degrees. Mounted with four hinges, and can be mounted to open from the left or right. (Machining is not required.) Includes door frame with 25 mm hole pattern

Zinc plated steel hinges with captive pin. Internally mounted door hinges prevent particulates from accumulating, making the enclosure easy to clean.

The one-piece, removable blue silicone gasket with molded corners helps ensure proper sealing, mitigating the possibility of liquid entry. It also is easy to replace, clean, maintain and install, and resists bacteria growth and chemical absorption. The silicone is FDA 21 CFR 177.2600 compliant.

HD lock made of stainless steel AISI 316L with blue silicone gasket, the lock conforms with norm DIN EN 1672-2:2009. Espagnolette 4-point locking system. Does not interfere with the enclosure inner space

No openings as standard to avoid hygiene risks

Door is equipped with separate welded earthing studs. Earthing to the frame can be accomplished by using the ECF

Complies with IP66/69 | IK10

400 pre-grained stainless steel, polished to Ra < 0.8 µm

Material: Stainless Steel 304
Finish: Brushed

Thickness: 1.5mm
Degree of Slope: 30°

SPECIFICATIONS

Catalog Number	Height	Height 1	Width	Depth	Protection Rating	Max Subpanel Size
HDF18065	1801mm	2132mm	600mm	514mm	NEMA Type 4, NEMA Type 4X, NEMA Type 12, IP66, IP69K, IP69K	1694 x 694mm
HDF18085	1801mm	2132mm	800mm	514mm	NEMA Type 4, NEMA Type 4X, NEMA Type 12, IP66, IP69K, IP69K	1694 x 694mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.