

# PEMSA Wire Basket Tray



The PEMS Wire Basket Tray is the backbone of PEMS Wire Basket Tray System. Highly engineered features help ensure a secure installation that complies with industry codes and standards for high-performance cables. Clever design allows the installer to maximize field efficiency with the Rejoband Rapide Integrated Splice.

## FEATURES

Provides optimal support for high-performance low voltage and data cables

Innovative Rejoband Rapide installation system

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic



## SPECIFICATIONS

Table 1/6

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT100X100BA   | 823011         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 100 mm     |
| WBT100X100BG   | 823012         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X100EG   | 823010         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X100S4   | 823013         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 100 mm     |
| WBT100X150BA   | 823021         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 100 mm     |
| WBT100X150BG   | 823022         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X150EG   | 823020         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X150S4   | 823023         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 100 mm     |
| WBT100X200BA   | 823031         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 100 mm     |
| WBT100X200BG   | 823032         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X200EG   | 823030         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X200S4   | 823033         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 100 mm     |
| WBT100X300BA   | 823041         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 100 mm     |

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT100X300BG   | 823042         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X300EG   | 823040         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X300S4   | 823043         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 100 mm     |
| WBT100X400BA   | 823051         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 100 mm     |
| WBT100X400BG   | 823052         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X400EG   | 823050         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X400S4   | 823053         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 100 mm     |

Table 2/6

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT100X450BA   | 823081         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 100 mm     |
| WBT100X450BG   | 823082         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X450EG   | 823080         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X500BA   | 823061         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 100 mm     |
| WBT100X500BG   | 823062         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X500EG   | 823060         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X500S4   | 823063         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 100 mm     |
| WBT100X600BA   | 823071         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 100 mm     |
| WBT100X600BG   | 823072         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X600EG   | 823070         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 100 mm     |
| WBT100X600S4   | 823073         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 100 mm     |
| WBT150X200BA   | 825031         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 150 mm     |
| WBT150X200BG   | 825032         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X200EG   | 825030         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X200S4   | 825033         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 150 mm     |
| WBT150X300BA   | 825041         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 150 mm     |
| WBT150X300BG   | 825042         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X300EG   | 825040         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X300S4   | 825043         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 150 mm     |
| WBT150X400BA   | 825051         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 150 mm     |

Table 3/6

| Catalog Number | Article Number | Color | Material     | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|--------------|-------------------|------------|------------|
| WBT150X400BG   | 825052         | Black | Carbon Steel | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X400EG   | 825050         |       | Carbon Steel | Electrogalvanized | 3000mm     | 150 mm     |

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT150X400S4   | 825053         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 150 mm     |
| WBT150X450BA   | 825081         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 150 mm     |
| WBT150X450BG   | 825082         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X450EG   | 825080         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X450S4   | 825083         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 150 mm     |
| WBT150X500BA   | 825061         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 150 mm     |
| WBT150X500BG   | 825062         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X500EG   | 825060         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X500S4   | 825063         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 150 mm     |
| WBT150X600BA   | 825071         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 150 mm     |
| WBT150X600BG   | 825072         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X600EG   | 825070         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X600S4   | 825073         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 150 mm     |
| WBT150X900BA   | 825091         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 150 mm     |
| WBT150X900BG   | 825092         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT150X900EG   | 825090         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 150 mm     |
| WBT35X100BA    | 821011         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 35 mm      |
| WBT35X100EG    | 821010         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 35 mm      |

Table 4/6

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT35X100S4    | 821013         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 35 mm      |
| WBT35X150BA    | 821021         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 35 mm      |
| WBT35X150EG    | 821020         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 35 mm      |
| WBT35X150S4    | 821023         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 35 mm      |
| WBT35X200BA    | 821031         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 35 mm      |
| WBT35X200EG    | 821030         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 35 mm      |
| WBT35X200S4    | 821033         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 35 mm      |
| WBT35X300BA    | 821041         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 35 mm      |
| WBT35X300EG    | 821040         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 35 mm      |
| WBT35X300S4    | 821043         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 35 mm      |
| WBT35X400BA    | 821051         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 35 mm      |
| WBT35X400EG    | 821050         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 35 mm      |
| WBT35X400S4    | 821053         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 35 mm      |
| WBT35X60BA     | 821001         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 35 mm      |

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT35X60EG     | 821000         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 35 mm      |
| WBT35X60S4     | 821003         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 35 mm      |
| WBT60X100BA    | 820011         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |
| WBT60X100BG    | 820012         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X100EG    | 820010         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X100S4    | 820013         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 60 mm      |

Table 5/6

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT60X150BA    | 820021         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |
| WBT60X150BG    | 820022         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X150EG    | 820020         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X150S4    | 820023         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 60 mm      |
| WBT60X200BA    | 820031         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |
| WBT60X200BG    | 820032         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X200EG    | 820030         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X200S4    | 820033         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 60 mm      |
| WBT60X300BA    | 820041         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |
| WBT60X300BG    | 820042         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X300EG    | 820040         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X300S4    | 820043         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 60 mm      |
| WBT60X400BA    | 820051         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |
| WBT60X400BG    | 820052         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X400EG    | 820050         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X400S4    | 820053         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 60 mm      |
| WBT60X450BA    | 820081         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |
| WBT60X450BG    | 820082         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X450EG    | 820080         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X500BA    | 820061         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |

Table 6/6

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT60X500BG    | 820062         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X500EG    | 820060         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X500S4    | 820063         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 60 mm      |
| WBT60X600BA    | 820075         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |

| Catalog Number | Article Number | Color | Material                        | Finish            | Length (L) | Height (H) |
|----------------|----------------|-------|---------------------------------|-------------------|------------|------------|
| WBT60X600BG    | 820076         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X600EG    | 820074         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X600S4    | 820077         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 60 mm      |
| WBT60X60BA     | 820001         | Black | Carbon Steel                    | Powder Coated     | 3000mm     | 60 mm      |
| WBT60X60BG     | 820002         | Black | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X60EG     | 820000         |       | Carbon Steel                    | Electrogalvanized | 3000mm     | 60 mm      |
| WBT60X60S4     | 820003         |       | Stainless Steel 304 (EN 1.4301) |                   | 3000mm     | 60 mm      |

Table 1/6

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                                                |
|----------------|----------------|-----------|-------------|-------------------------------------------------------------------------------|
| WBT100X100BA   | 823011         | 100 mm    | 3.27 kg     |                                                                               |
| WBT100X100BG   | 823012         | 100 mm    | 3.27 kg     | CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT, DoP, CADDY EU WBT |
| WBT100X100EG   | 823010         | 100 mm    | 3.27 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG |
| WBT100X100S4   | 823013         | 100 mm    | 3.27 kg     | DoP, CADDY EU WBT, UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG |
| WBT100X150BA   | 823021         | 150 mm    | 3.45 kg     |                                                                               |
| WBT100X150BG   | 823022         | 150 mm    | 3.45 kg     | DoP, CADDY EU WBT, UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG |
| WBT100X150EG   | 823020         | 150 mm    | 3.45 kg     | DoP, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT |
| WBT100X150S4   | 823023         | 150 mm    | 3.45 kg     | DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT |
| WBT100X200BA   | 823031         | 200 mm    | 4.14 kg     |                                                                               |
| WBT100X200BG   | 823032         | 200 mm    | 4.14 kg     | DoP, CADDY EU WBT, CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG |
| WBT100X200EG   | 823030         | 200 mm    | 4.14 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT |
| WBT100X200S4   | 823033         | 200 mm    | 4.14 kg     | ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, DoP, CADDY EU WBT, UKCA, CADDY EU WBT |
| WBT100X300BA   | 823041         | 300 mm    | 6.15 kg     |                                                                               |
| WBT100X300BG   | 823042         | 300 mm    | 6.15 kg     | CE, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT |
| WBT100X300EG   | 823040         | 300 mm    | 6.15 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT |
| WBT100X300S4   | 823043         | 300 mm    | 6.15 kg     | UKCA, CADDY EU WBT, DoP, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG |

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                                                |
|----------------|----------------|-----------|-------------|-------------------------------------------------------------------------------|
| WBT100X400BA   | 823051         | 400 mm    | 7.23 kg     |                                                                               |
| WBT100X400BG   | 823052         | 400 mm    | 7.23 kg     | ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT, DoP, CADDY EU WBT |
| WBT100X400EG   | 823050         | 400 mm    | 7.23 kg     | DoP, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT |
| WBT100X400S4   | 823053         | 400 mm    | 7.23 kg     | DoP, CADDY EU WBT, CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG |

| Table 2/6      |                |           |             |                                                                               |
|----------------|----------------|-----------|-------------|-------------------------------------------------------------------------------|
| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                                                |
| WBT100X450BA   | 823081         | 450 mm    | 7.44 kg     |                                                                               |
| WBT100X450BG   | 823082         | 450 mm    | 7.44 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG                    |
| WBT100X450EG   | 823080         | 450 mm    | 7.44 kg     | UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT |
| WBT100X500BA   | 823061         | 500 mm    | 8.34 kg     |                                                                               |
| WBT100X500BG   | 823062         | 500 mm    | 8.34 kg     | UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT                    |
| WBT100X500EG   | 823060         | 500 mm    | 8.34 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG                    |
| WBT100X500S4   | 823063         | 500 mm    | 8.34 kg     | ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT, CE, CADDY EU WBT                    |
| WBT100X600BA   | 823071         | 600 mm    | 9.42 kg     |                                                                               |
| WBT100X600BG   | 823072         | 600 mm    | 9.42 kg     | ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT                    |
| WBT100X600EG   | 823070         | 600 mm    | 9.42 kg     | UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT                    |
| WBT100X600S4   | 823073         | 600 mm    | 9.42 kg     | CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT                    |
| WBT150X200BA   | 825031         | 200 mm    | 6.01 kg     |                                                                               |
| WBT150X200BG   | 825032         | 200 mm    | 6.01 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT                                          |
| WBT150X200EG   | 825030         | 200 mm    | 6.01 kg     | DoP, CADDY EU WBT, UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT150X200S4   | 825033         | 200 mm    | 6.01 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT                                          |
| WBT150X300BA   | 825041         | 300 mm    | 7.29 kg     |                                                                               |
| WBT150X300BG   | 825042         | 300 mm    | 7.29 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT                                          |
| WBT150X300EG   | 825040         | 300 mm    | 7.29 kg     | DoP, CADDY EU WBT, UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT150X300S4   | 825043         | 300 mm    | 7.29 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT                                          |

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications |
|----------------|----------------|-----------|-------------|----------------|
| WBT150X400BA   | 825051         | 400 mm    | 8.47 kg     |                |

Table 3/6

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                             |
|----------------|----------------|-----------|-------------|------------------------------------------------------------|
| WBT150X400BG   | 825052         | 400 mm    | 8.47 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT                       |
| WBT150X400EG   | 825050         | 400 mm    | 8.47 kg     | CE, CADDY EU WBT, DoP, CADDY EU WBT, UKCA, CADDY EU WBT    |
| WBT150X400S4   | 825053         | 400 mm    | 8.47 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT                       |
| WBT150X450BA   | 825081         | 450 mm    | 8.68 kg     |                                                            |
| WBT150X450BG   | 825082         | 450 mm    | 8.68 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT                       |
| WBT150X450EG   | 825080         | 450 mm    | 8.68 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT150X450S4   | 825083         | 450 mm    | 8.68 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT150X500BA   | 825061         | 500 mm    | 9.7 kg      |                                                            |
| WBT150X500BG   | 825062         | 500 mm    | 9.7 kg      | CE, CADDY EU WBT, UKCA, CADDY EU WBT                       |
| WBT150X500EG   | 825060         | 500 mm    | 9.7 kg      | UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT150X500S4   | 825063         | 500 mm    | 9.7 kg      | UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT150X600BA   | 825071         | 600 mm    | 10.65 kg    |                                                            |
| WBT150X600BG   | 825072         | 600 mm    | 10.65 kg    | UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT150X600EG   | 825070         | 600 mm    | 10.65 kg    | UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT150X600S4   | 825073         | 600 mm    | 10.65 kg    | CE, CADDY EU WBT, UKCA, CADDY EU WBT                       |
| WBT150X900BA   | 825091         | 900 mm    | 15.98 kg    |                                                            |
| WBT150X900BG   | 825092         | 900 mm    | 15.98 kg    |                                                            |
| WBT150X900EG   | 825090         | 900 mm    | 15.98 kg    |                                                            |
| WBT35X100BA    | 821011         | 100 mm    | 1.62 kg     |                                                            |
| WBT35X100EG    | 821010         | 100 mm    | 1.62 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG |

Table 4/6

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                             |
|----------------|----------------|-----------|-------------|------------------------------------------------------------|
| WBT35X100S4    | 821013         | 100 mm    | 1.61 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |
| WBT35X150BA    | 821021         | 150 mm    | 1.76 kg     |                                                            |
| WBT35X150EG    | 821020         | 150 mm    | 1.76 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG |
| WBT35X150S4    | 821023         | 150 mm    | 2.12 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT                       |

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                                                |
|----------------|----------------|-----------|-------------|-------------------------------------------------------------------------------|
| WBT35X200BA    | 821031         | 200 mm    | 2.5 kg      |                                                                               |
| WBT35X200EG    | 821030         | 200 mm    | 2.5 kg      | ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT                    |
| WBT35X200S4    | 821033         | 200 mm    | 3.04 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG                    |
| WBT35X300BA    | 821041         | 300 mm    | 3.42 kg     |                                                                               |
| WBT35X300EG    | 821040         | 300 mm    | 3.42 kg     | CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT                    |
| WBT35X300S4    | 821043         | 300 mm    | 4.13 kg     | ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT, CE, CADDY EU WBT                    |
| WBT35X400BA    | 821051         | 400 mm    | 4.29 kg     |                                                                               |
| WBT35X400EG    | 821050         | 400 mm    | 4.29 kg     | ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT, CE, CADDY EU WBT                    |
| WBT35X400S4    | 821053         | 400 mm    | 5.22 kg     | CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT                    |
| WBT35X60BA     | 821001         | 60 mm     | 1.2 kg      |                                                                               |
| WBT35X60EG     | 821000         | 60 mm     | 1.2 kg      | UKCA, CADDY EU WBT, CE, CADDY EU WBT                                          |
| WBT35X60S4     | 821003         | 60 mm     | 1.19 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT                                          |
| WBT60X100BA    | 820011         | 100 mm    | 2.43 kg     |                                                                               |
| WBT60X100BG    | 820012         | 100 mm    | 2.43 kg     | DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT, CE, CADDY EU WBT |
| WBT60X100EG    | 820010         | 100 mm    | 2.43 kg     | ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT, UKCA, CADDY EU WBT, CE, CADDY EU WBT |
| WBT60X100S4    | 820013         | 100 mm    | 2.43 kg     | UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT |

Table 5/6

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                                                |
|----------------|----------------|-----------|-------------|-------------------------------------------------------------------------------|
| WBT60X150BA    | 820021         | 150 mm    | 2.6 kg      |                                                                               |
| WBT60X150BG    | 820022         | 150 mm    | 2.6 kg      | UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT |
| WBT60X150EG    | 820020         | 150 mm    | 2.6 kg      | DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT |
| WBT60X150S4    | 820023         | 150 mm    | 2.6 kg      | CE, CADDY EU WBT, ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT, DoP, CADDY EU WBT |
| WBT60X200BA    | 820031         | 200 mm    | 3.33 kg     |                                                                               |
| WBT60X200BG    | 820032         | 200 mm    | 3.33 kg     | DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT |



| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                                                |
|----------------|----------------|-----------|-------------|-------------------------------------------------------------------------------|
| WBT60X200EG    | 820030         | 200 mm    | 3.33 kg     | UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT |
| WBT60X200S4    | 820033         | 200 mm    | 3.33 kg     | DoP, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT |
| WBT60X300BA    | 820041         | 300 mm    | 5.13 kg     |                                                                               |
| WBT60X300BG    | 820042         | 300 mm    | 5.13 kg     | ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT, CE, CADDY EU WBT, DoP, CADDY EU WBT |
| WBT60X300EG    | 820040         | 300 mm    | 5.13 kg     | DoP, CADDY EU WBT, CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG |
| WBT60X300S4    | 820043         | 300 mm    | 5.13 kg     | ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT, UKCA, CADDY EU WBT, CE, CADDY EU WBT |
| WBT60X400BA    | 820051         | 400 mm    | 6.21 kg     |                                                                               |
| WBT60X400BG    | 820052         | 400 mm    | 6.21 kg     | UKCA, CADDY EU WBT, DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT |
| WBT60X400EG    | 820050         | 400 mm    | 6.21 kg     | UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT, CE, CADDY EU WBT |
| WBT60X400S4    | 820053         | 400 mm    | 6.21 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG                    |
| WBT60X450BA    | 820081         | 450 mm    | 6.39 kg     |                                                                               |
| WBT60X450BG    | 820082         | 450 mm    | 6.39 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG                    |
| WBT60X450EG    | 820080         | 450 mm    | 6.39 kg     | DoP, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT |
| WBT60X500BA    | 820061         | 500 mm    | 7.35 kg     |                                                                               |

Table 6/6

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                                                |
|----------------|----------------|-----------|-------------|-------------------------------------------------------------------------------|
| WBT60X500BG    | 820062         | 500 mm    | 7.35 kg     | UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT                    |
| WBT60X500EG    | 820060         | 500 mm    | 7.35 kg     | ANOR EU WTB EG S4 BG, UKCA, CADDY EU WBT, CE, CADDY EU WBT                    |
| WBT60X500S4    | 820063         | 500 mm    | 7.35 kg     | UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT                    |
| WBT60X600BA    | 820075         | 600 mm    | 8.43 kg     |                                                                               |
| WBT60X600BG    | 820076         | 600 mm    | 8.43 kg     | UKCA, CADDY EU WBT, ANOR EU WTB EG S4 BG, CE, CADDY EU WBT                    |
| WBT60X600EG    | 820074         | 600 mm    | 8.43 kg     | ANOR EU WTB EG S4 BG, CE, CADDY EU WBT, UKCA, CADDY EU WBT                    |
| WBT60X600S4    | 820077         | 600 mm    | 8.43 kg     | ANOR EU WTB EG S4 BG, DoP, CADDY EU WBT, UKCA, CADDY EU WBT, CE, CADDY EU WBT |

| Catalog Number | Article Number | Width (W) | Unit Weight | Certifications                                             |
|----------------|----------------|-----------|-------------|------------------------------------------------------------|
| WBT60X60BA     | 820001         | 60 mm     | 2.32 kg     |                                                            |
| WBT60X60BG     | 820002         | 60 mm     | 2.32 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG |
| WBT60X60EG     | 820000         | 60 mm     | 2.32 kg     | UKCA, CADDY EU WBT, CE, CADDY EU WBT, ANOR EU WTB EG S4 BG |
| WBT60X60S4     | 820003         | 60 mm     | 2.32 kg     | CE, CADDY EU WBT, UKCA, CADDY EU WBT                       |

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

