

# Wire Basket Tray PreForm Tee



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

## FEATURES

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

**Material:** Steel  
**Finish:** Pregalvanized; Polyurethane



## SPECIFICATIONS

Table 1/2

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Radius (R) | Unit Weight |
|----------------|-------|------------|-----------|------------|----------------|------------|-------------|
| WBTT2X12       |       | 50.8 mm    | 515.62 mm | 711.2mm    | 19.05 mm       | 94.64mm    | 2.722 kg    |
| WBTT2X12BA     | Black | 50.8 mm    | 515.62 mm | 711.2mm    | 19.05 mm       | 94.64mm    | 2.722 kg    |
| WBTT2X18       |       | 50.8 mm    | 668.02 mm | 863.6mm    | 19.05 mm       | 94.64mm    | 4.536 kg    |
| WBTT2X18BA     | Black | 50.8 mm    | 668.02 mm | 863.6mm    | 19.05 mm       | 94.64mm    | 4.536 kg    |

| Catalog Number | Color | Height (H)            | Width (W) | Length (L) | Hole Size(HS) | Radius(R) | UnitWeight |
|----------------|-------|-----------------------|-----------|------------|---------------|-----------|------------|
| WBTT2X24       |       | 50.8 mm               | 817.88 mm | 1013.46mm  | 19.05 mm      | 94.64mm   | 7.257 kg   |
| WBTT2X24BA     | Black | 50.8 mm               | 817.88 mm | 1013.46mm  | 19.05 mm      | 94.64mm   | 7.257 kg   |
| WBTT2X4        |       | 50.8 mm               | 317.5 mm  | 513.08mm   |               | 94.64mm   | 0.454 kg   |
| WBTT2X4BA      | Black | 50.8 mm               | 317.5 mm  | 513.08mm   |               | 94.64mm   | 0.454 kg   |
| WBTT2X6        |       | 50.8 mm               | 365.76 mm | 561.34mm   |               | 94.64mm   | 1.361 kg   |
| WBTT2X6BA      | Black | 50.8 mm               | 365.76 mm | 561.34mm   |               | 94.64mm   | 1.361 kg   |
| WBTT2X8        |       | 50.8 mm               | 416.56 mm | 612.14mm   |               | 94.64mm   | 1.814 kg   |
| WBTT2X8BA      | Black | 50.8 mm               | 416.56 mm | 612.14mm   |               | 94.64mm   | 1.814 kg   |
| WBTT6X6        |       | 152.39999999999998 mm |           |            |               |           |            |
| WBTT2X4S4      |       | 50.8 mm               |           |            |               |           |            |
| WBTT4X12       |       | 101.6 mm              |           |            |               |           |            |
| WBTT4X12BA     | Black | 101.6 mm              |           |            |               |           |            |
| WBTT4X18       |       | 101.6 mm              |           |            |               |           |            |
| WBTT4X18BA     | Black | 101.6 mm              |           |            |               |           |            |
| WBTT4X24       |       | 101.6 mm              |           |            |               |           |            |
| WBTT4X24BA     | Black | 101.6 mm              |           |            |               |           |            |

Table 2/2

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Radius (R) | Unit Weight |
|----------------|-------|------------|-----------|------------|----------------|------------|-------------|
| WBTT4X4        |       | 101.6 mm   |           |            |                |            |             |
| WBTT4X4BA      | Black | 101.6 mm   |           |            |                |            |             |
| WBTT4X6        |       | 101.6 mm   |           |            |                |            |             |
| WBTT4X6BA      | Black | 101.6 mm   |           |            |                |            |             |
| WBTT6X12       |       | 152.4 mm   |           |            |                |            |             |
| WBTT6X12BA     | Black | 152.4 mm   |           |            |                |            |             |
| WBTT6X18       |       | 152.4 mm   |           |            |                |            |             |
| WBTT6X18BA     | Black | 152.4 mm   |           |            |                |            |             |
| WBTT6X24       |       | 152.4 mm   |           |            |                |            |             |
| WBTT6X24BA     | Black | 152.4 mm   |           |            |                |            |             |
| WBTT6X36       |       | 152.4 mm   |           |            |                |            |             |

WARNING

---

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

