


# Mounting Plates Wall Mounted Enclosures, AMP

The steel mounting plate contributes to speeding up the assembly of the enclosure, since it can be machined easily and equipped with components before being mounted.



## FEATURES

Description: Steel mounting plate for wall mounted enclosures. All sizes from 800 mm and above are strengthened by folded edges. By using the AMG accessory, the mounting plate position can be adjusted to any depth. This accessory is not suitable for the AFS range of enclosures, please refer to the replacement and spare parts catalogue.

Material: Galvanized steel.

Pack quantity: 1 piece.

**Material:** Mild Steel  
**Finish:** Galvanized  
**Thickness:** 2mm

## SPECIFICATIONS

Table 1/2

| Catalog Number | Height | Width  | Depth | Panel Size    | Enclosure Material |
|----------------|--------|--------|-------|---------------|--------------------|
| AMP10100       | 1000mm | 999mm  | 12mm  | 970 x 950mm   | Mild Steel         |
| AMP10120       | 1000mm | 1199mm | 12mm  | 970 x 950mm   | Mild Steel         |
| AMP12120       | 1200mm | 1199mm | 12mm  | 1170 x 1150mm | Mild Steel         |
| AMP02020       | 200mm  | 199mm  | 2mm   | 170 x 150mm   | Mild Steel         |
| AMP02520       | 250mm  | 199mm  | 2mm   | 220 x 150mm   | Mild Steel         |
| AMP02525       | 250mm  | 249mm  | 2mm   | 220 x 200mm   | Mild Steel         |
| AMP03025       | 300mm  | 249mm  | 2mm   | 270 x 200mm   | Mild Steel         |
| AMP03030       | 300mm  | 299mm  | 2mm   | 270 x 250mm   | Mild Steel         |
| AMP03040       | 300mm  | 400mm  | 2mm   | 270 x 350mm   | Mild Steel         |
| AMP03060       | 300mm  | 599mm  | 2mm   | 270 x 550mm   | Mild Steel         |

| Catalog Number | Height | Width  | Depth | Panel Size   | Enclosure Material |
|----------------|--------|--------|-------|--------------|--------------------|
| AMP03080       | 300mm  | 799mm  | 2mm   | 270 x 750mm  | Mild Steel         |
| AMP03100       | 300mm  | 999mm  | 12mm  | 270 x 950mm  | Mild Steel         |
| AMP03120       | 300mm  | 1199mm | 12mm  | 270 x 1150mm | Mild Steel         |
| AMP03525       | 350mm  | 249mm  | 2mm   | 320 x 200mm  | Mild Steel         |
| AMP04030       | 400mm  | 299mm  | 2mm   | 370 x 250mm  | Mild Steel         |
| AMP04040       | 400mm  | 400mm  | 2mm   | 370 x 350mm  | Mild Steel         |
| AMP04050       | 400mm  | 500mm  | 2mm   | 370 x 450mm  | Mild Steel         |
| AMP04060       | 400mm  | 599mm  | 2mm   | 370 x 550mm  | Mild Steel         |
| AMP05030       | 500mm  | 299mm  | 2mm   | 470 x 250mm  | Mild Steel         |
| AMP05040       | 500mm  | 350mm  | 2mm   | 470 x 350mm  | Mild Steel         |

Table 2/2

| Catalog Number | Height | Width  | Depth | Panel Size   | Enclosure Material |
|----------------|--------|--------|-------|--------------|--------------------|
| AMP05050       | 500mm  | 500mm  | 2mm   | 470 x 450mm  | Mild Steel         |
| AMP06040       | 600mm  | 400mm  | 2mm   | 570 x 350mm  | Mild Steel         |
| AMP06050       | 600mm  | 500mm  | 2mm   | 570 x 450mm  | Mild Steel         |
| AMP06060       | 600mm  | 599mm  | 2mm   | 570 x 550mm  | Mild Steel         |
| AMP06080       | 600mm  | 799mm  | 2mm   | 570 x 750mm  | Mild Steel         |
| AMP07050       | 700mm  | 500mm  | 2mm   | 670 x 450mm  | Mild Steel         |
| AMP08040       | 800mm  | 400mm  | 12mm  | 770 x 350mm  | Mild Steel         |
| AMP08060       | 800mm  | 599mm  | 12mm  | 770 x 550mm  | Mild Steel         |
| AMP08080       | 800mm  | 799mm  | 12mm  | 770 x 750mm  | Mild Steel         |
| AMP08120       | 800mm  | 1199mm | 12mm  | 770 x 1150mm | Mild Steel         |
| AMP10060       | 1000mm | 599mm  | 12mm  | 970 x 550mm  | Mild Steel         |
| AMP10080       | 1000mm | 799mm  | 12mm  | 970 x 750mm  | Mild Steel         |
| AMP12060       | 1200mm | 599mm  | 12mm  | 1170 x 550mm | Mild Steel         |
| AMP12080       | 1200mm | 799mm  | 12mm  | 1170 x 750mm | Mild Steel         |
| AMP12100       | 1200mm | 999mm  | 12mm  | 1170 x 950mm | Mild Steel         |
| AMP14100       | 1400mm | 999mm  | 12mm  | 1370 x 950mm | Mild Steel         |

## ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.