


Assembly Part



The flat underside and large bearing surface of a cheese head screw spread the clamping force over a wider area than many low-profile heads. This helps reduce surface damage on softer materials and prevent the head from sinking into plastics, aluminum, or thin sheet metal.

FEATURES

- Screw to fix front handle, Tip-up carrying feet, PMC Mezzanine or HF cassettes
- Slotted head requires flat-bladed screwdriver that enhances rotational leverage and simplify the installation process for fasteners

Product Type: Screw
Type: Screw



SPECIFICATIONS

Catalog Number	Length	Material	Finish	Package Quantity	Thread Size	Works With	Thread Length
21101-211	12mm	Steel	Zinc Plated	100	M4	Front Panels	12mm
21100-624	5mm	Steel	Nickel Plated	100	M2.5	Front Panels	5mm
21100-431	4mm	Steel	Nickel Plated	100	M2.5	Front Panels	4mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

