

PBF Two Hole Base Plate for Threaded Rod, Steel, EG, M8, M10 Rod, 120 mm

CATALOG NUMBER

PBRM8M10L120

FEATURES

Light duty with two holes and one nut/adaptor



PRODUCT ATTRIBUTES

Article Number: 587140

Material: Steel

Finish: Electrogalvanized

Rod Size (RS): 8;10

Length (L): 120mm

Width (W): 40 mm

Thickness (T): 4 mm

A: 81 mm

B: 18 mm

C: 11 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

