

Heavy Duty Pipe Clamp, Painted, Red Oxide, 403–410 mm OD, 16" Pipe, 400 DN

CATALOG NUMBER

SSG410R0

FEATURES

For high static requirements in industrial construction

Suitable for fix point applications



PRODUCT ATTRIBUTES

Article Number: 574730

Material: Steel

Finish: Painted;Red Oxide

Outer Diameter (OD): 403 - 410 mm

Pipe Size: 16"

NB/DN: 400

Hole Size (HS): 26 mm

Screw Diameter (Sc): 24 mm

Screw Length (L): 80mm

Static Load: 4100N

Width (W): 70 mm

Thickness (T): 10 mm

A: 492 mm

ADDITIONAL PRODUCT DETAILS

Static load refers to a complete set of Heavy Duty Pipe Clamps held in place with indicated screws per ISO 4014 and corresponding hex nuts per ISO 4032 (for further information, please refer to Standard SSG 7075E).

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

