

Speedway Cable Ladder Outside Riser, 45°



FEATURES

Creates a 45° outside riser elevation change for cable tray

Provides optimal support for high-performance low voltage and data cables

Innovative SPEEDLOK integrated coupling system

Safety edge protects cables during installation

Slotted side channel, eliminating field drilling for cut-to-length applications

IEC 61537 load rating and earthing compliant

Responsive design and layout services, including seismic


Material: Steel
Finish: Hot-Dip Galvanized



SPECIFICATIONS

Catalog Number	Article Number	Width (W)	Angle (a)	A	B	C
CL110X150OR45HD	840400	150 mm	45 °	198 mm	290 mm	80 mm
CL110X300OR45HD	840410	300 mm	45 °	198 mm	290 mm	80 mm
CL110X450OR45HD	840420	450 mm	45 °	198 mm	290 mm	80 mm
CL110X600OR45HD	840430	600 mm	45 °	198 mm	290 mm	80 mm
CL110X750OR45HD	840440	750 mm	45 °	198 mm	290 mm	80 mm
CL110X900OR45HD	840450	900 mm	45 °	198 mm	290 mm	80 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

