

# VDF TORX Wood-to-Metal Screw with TORX® Head



## FEATURES

Wood dowel screw with metric thread connection

TORX® head

## SPECIFICATIONS

Table 1/2

| Catalog Number | Article Number | Material                        | Finish            | Screw Diameter (Sc) | Length (L) | A     |
|----------------|----------------|---------------------------------|-------------------|---------------------|------------|-------|
| VDFM10050      | 593560         | Steel                           | Electrogalvanized | 10                  | 50mm       | 30 mm |
| VDFM10060      | 593330         | Steel                           | Electrogalvanized | 10                  | 60mm       | 30 mm |
| VDFM10080      | 593340         | Steel                           | Electrogalvanized | 10                  | 80mm       | 40 mm |
| VDFM10100      | 593350         | Steel                           | Electrogalvanized | 10                  | 100mm      | 60 mm |
| VDFM10100S4    | 400482         | Stainless Steel 304 (EN 1.4301) |                   | 10                  | 100mm      | 55 mm |
| VDFM10120      | 593370         | Steel                           | Electrogalvanized | 10                  | 120mm      | 60 mm |
| VDFM10150      | 593570         | Steel                           | Electrogalvanized | 10                  | 150mm      | 60 mm |

| Catalog Number | Article Number | Material                        | Finish            | Screw Diameter (Sc) | Length(L) | A     |
|----------------|----------------|---------------------------------|-------------------|---------------------|-----------|-------|
| VDFM12120      | 400403         | Steel                           | Electrogalvanized | 12                  | 120mm     | 55 mm |
| VDFM8050       | 593270         | Steel                           | Electrogalvanized | 8                   | 50mm      | 40 mm |
| VDFM8050S4     | 400477         | Stainless Steel 304 (EN 1.4301) |                   | 8                   | 50mm      | 28 mm |
| VDFM8060       | 593280         | Steel                           | Electrogalvanized | 8                   | 60mm      | 30 mm |
| VDFM8070       | 593290         | Steel                           | Electrogalvanized | 8                   | 70mm      | 30 mm |
| VDFM8080       | 593300         | Steel                           | Electrogalvanized | 8                   | 80mm      | 40 mm |
| VDFM8080S4     | 400478         | Stainless Steel 304 (EN 1.4301) |                   | 8                   | 80mm      | 40 mm |
| VDFM8100       | 593310         | Steel                           | Electrogalvanized | 8                   | 100mm     | 40 mm |
| VDFM8120       | 593400         | Steel                           | Electrogalvanized | 8                   | 120mm     | 50 mm |
| VDFM8150       | 593410         | Steel                           | Electrogalvanized | 8                   | 150mm     | 45 mm |
| VDFM8200       | 593420         | Steel                           | Electrogalvanized | 8                   | 200mm     | 50 mm |

Table 2/2

| Catalog Number | Article Number | C     | TORX® |
|----------------|----------------|-------|-------|
| VDFM10050      | 593560         | 18 mm | T25   |
| VDFM10060      | 593330         | 18 mm | T25   |
| VDFM10080      | 593340         | 30 mm | T25   |
| VDFM10100      | 593350         | 30 mm | T25   |
| VDFM10100S4    | 400482         | 40 mm | T25   |
| VDFM10120      | 593370         | 50 mm | T25   |
| VDFM10150      | 593570         | 50 mm | T25   |
| VDFM12120      | 400403         | 30 mm | T30   |
| VDFM8050       | 593270         | 10 mm | T25   |
| VDFM8050S4     | 400477         | 15 mm | T25   |
| VDFM8060       | 593280         | 20 mm | T25   |
| VDFM8070       | 593290         | 25 mm | T25   |
| VDFM8080       | 593300         | 30 mm | T25   |


| Catalog Number | Article Number | C     | TORX® |
|----------------|----------------|-------|-------|
| VDFM8080S4     | 400478         | 30 mm | T25   |
| VDFM8100       | 593310         | 40 mm | T25   |
| VDFM8120       | 593400         | 50 mm | T25   |
| VDFM8150       | 593410         | 50 mm | T25   |
| VDFM8200       | 593420         | 50 mm | T25   |

## ADDITIONAL PRODUCT DETAILS

No HEX when length is 50.0 mm.

No TORX® head with the stainless steel screws.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

