

C-Channel 2-2 Open Corner Angle Bracket

FEATURES

Universally applicable for the construction of assembly systems



Material: Steel
Finish: Electrogalvanized


SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Channel Type	Angle (a)	A	B	C
EBL25A135	584668	E0, E0L, E1	135 °	25 mm	88 mm	4 mm
EBL35A135	587520	E2, E2L, E3, E4	135 °	35 mm	88 mm	4 mm

Table 2/2

Catalog Number	Article Number	D	Hole Size (HS)
EBL25A135	584668	44 mm	10.5 mm
EBL35A135	587520	44 mm	10.5 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

