

# C-EU Single Cable to Flange Clamp



## FEATURES

Supports single run of conduit

Attaches to beam flanges, angle iron, joists and other structural supports

**Material:** Steel  
**Finish:** Hot-Dip Galvanized

## SPECIFICATIONS

| Catalog Number | Article Number | Outer Diameter (OD) | Flange Thickness (FT) | A         | Torque (TQ) |
|----------------|----------------|---------------------|-----------------------|-----------|-------------|
| C12EU          | 337300         | 8 - 12 mm           | 12 mm Max             | 41 mm Max | 2 N·m       |
| C16EU          | 337310         | 12 - 16 mm          | 12 mm Max             | 46 mm Max | 2 N·m       |
| C20EU          | 337320         | 16 - 20 mm          | 12 mm Max             | 50 mm Max | 2 N·m       |
| C24EU          | 337330         | 20 - 24 mm          | 12 mm Max             | 54 mm Max | 2 N·m       |
| C28EU          | 337340         | 24 - 28 mm          | 12 mm Max             | 58 mm Max | 2 N·m       |
| C32EU          | 337350         | 28 - 32 mm          | 12 mm Max             | 63 mm Max | 2 N·m       |
| C36EU          | 337360         | 32 - 36 mm          | 12 mm Max             | 67 mm Max | 2 N·m       |
| C40EU          | 337370         | 36 - 40 mm          | 12 mm Max             | 71 mm Max | 2 N·m       |
| C44EU          | 337380         | 40 - 44 mm          | 12 mm Max             | 81 mm Max | 4 N·m       |
| C48EU          | 337390         | 44 - 48 mm          | 12 mm Max             | 85 mm Max | 4 N·m       |
| C52EU          | 337400         | 48 - 52 mm          | 12 mm Max             | 90 mm Max | 4 N·m       |
| C56EU          | 337410         | 52 - 56 mm          | 12 mm Max             | 94 mm Max | 4 N·m       |
| C60EU          | 337420         | 56 - 60 mm          | 12 mm Max             | 98 mm Max | 4 N·m       |

| Catalog Number | Article Number | Outer Diameter (OD) | Flange Thickness (FT) | A          | Torque (TQ) |
|----------------|----------------|---------------------|-----------------------|------------|-------------|
| C64EU          | 337430         | 60 - 64 mm          | 12 mm Max             | 102 mm Max | 4 N·m       |
| C70EU          | 337440         | 64 - 70 mm          | 12 mm Max             | 109 mm Max | 4 N·m       |
| C76EU          | 337450         | 70 - 76 mm          | 12 mm Max             | 113 mm Max | 4 N·m       |
| C82EU          | 337460         | 76 - 82 mm          | 12 mm Max             | 119 mm Max | 4 N·m       |

### ADDITIONAL PRODUCT DETAILS

Screw is electrogalvanized on clamps that have an outer diameter of 40 mm or less.

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

#### Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

#### Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

#### APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

