

Pipe/Cable Clamp, S304, 2" Pipe



CATALOG NUMBER

CR200S4

FEATURES

Captive threaded stud minimizes the need for additional hardware

With the UNICBAND Sign Support Bracket and Fixoband Strap, attachments to pipe and pole can be made

PRODUCT ATTRIBUTES

Article Number: 336460

Material: Stainless Steel 304 (EN 1.4301)

Pipe Size: 2" Min

NB/DN: 50

Outer Diameter (OD): 59.2 - 63.5 mm

Width (W): 20 mm

Static Load 1 (F1): 250N

Static Load 2 (F2): 550N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

