



**34560-140**

## FEATURES

< 28 HP not to print

Combinations of horizontal rails and side panels

|                    |                    | $\Delta T_{\text{max}}$ can be combined $\Delta T_{\text{max}}$ combination not recommended |                                          |                                          |                                          |
|--------------------|--------------------|---------------------------------------------------------------------------------------------|------------------------------------------|------------------------------------------|------------------------------------------|
| <br>Double glazing | <br>Single glazing | +                                                                                           | +                                        | +                                        | +                                        |
|                    | <br>Triple glazing | +                                                                                           | reduced Uf possible<br>(see calculation) | reduced Uf possible<br>(see calculation) | reduced Uf possible<br>(see calculation) |
| <br>Double glazing | <br>Single glazing | +                                                                                           | +                                        | +                                        | +                                        |
|                    | <br>Triple glazing | +                                                                                           | reduced Uf possible<br>(see calculation) | reduced Uf possible<br>(see calculation) | reduced Uf possible<br>(see calculation) |
| <br>Double glazing | <br>Single glazing | +                                                                                           | +                                        | +                                        | +                                        |
|                    | <br>Triple glazing | +                                                                                           | reduced Uf possible<br>(see calculation) | reduced Uf possible<br>(see calculation) | reduced Uf possible<br>(see calculation) |

## PRODUCT ATTRIBUTES

Gross Weight: 0.065kg



ADDITIONAL PRODUCT DETAILS

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

