

PBF Two Hole Base Plate for Threaded Rod

FEATURES

Light duty with two holes and one nut/adaptor



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	Material	Finish	Rod Size (RS)	Length (L)	Width (W)
PBRM10L120	587160	Steel	Electrogalvanized	10	120mm	40 mm
PBRM10L80	587135	Steel	Electrogalvanized	10	80mm	30 mm
PBRM12L120	587165	Steel	Electrogalvanized	12	120mm	40 mm
PBRM8M10L120	587140	Steel	Electrogalvanized	8, 10	120mm	40 mm
PBRM8M10L70S6	587175	Stainless Steel 316 (EN 1.4401)		8, 10	70mm	33 mm
PBRM8M10L80	587145	Steel	Electrogalvanized	8, 10	80mm	30 mm

Table 2/2

Catalog Number	Article Number	Thickness (T)	A	B	C
PBRM10L120	587160	4 mm	81 mm	18 mm	11 mm

Catalog Number	Article Number	Thickness (T)	A	B	C
PBRM10L80	587135	3 mm	50 mm	18 mm	9 mm
PBRM12L120	587165	4 mm	81 mm	18 mm	11 mm
PBRM8M10L120	587140	4 mm	81 mm	18 mm	11 mm
PBRM8M10L70S6	587175	2 mm	48 mm	10 mm	8 mm
PBRM8M10L80	587145	3 mm	50 mm	18 mm	9 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

