


U-Bolt

FEATURES

Complete with 4 nuts




SPECIFICATIONS

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)	Height (H)
UB4N017M6	599110	Steel	Electrogalvanized	17 mm	10	M6	42 mm
UB4N021M6	599120	Steel	Electrogalvanized	21 mm	15	M6	46 mm
UB4N021M8S6	599346	Stainless Steel 316 (EN 1.4401)		21 mm	15	M8	46 mm
UB4N027M8	599130	Steel	Electrogalvanized	27 mm	20	M8	58 mm
UB4N034M8	599140	Steel	Electrogalvanized	34 mm	25	M8	63 mm
UB4N049M8	599160	Steel	Electrogalvanized	49 mm	40	M8	78 mm
UB4N060M8S6	597655	Stainless Steel 316 (EN 1.4401)		60 mm	50	M8	88 mm
UB4N076M8	599180	Steel	Electrogalvanized	76 mm	65	M8	118 mm

Catalog Number	Article Number	Material	Finish	Outer Diameter (OD)	NB/D N	Rod Size (RS)	Height (H)
UB4N090M10	599190	Steel	Electrogalvanized	90 mm	80	M10	125 mm
UB4N160M8	599338	Steel	Electrogalvanized	160 mm		M8	214 mm
UB4N160M8S6	599351	Stainless Steel 316 (EN 1.4401)		160 mm		M8	214 mm
UB4N219M10S6	599354	Stainless Steel 316 (EN 1.4401)		219 mm	200	M10	286 mm
UB4N219M16	599250	Steel	Electrogalvanized	219 mm	200	M16	286 mm
UB4N273M10S6	599355	Stainless Steel 316 (EN 1.4401)		273 mm	250	M10	331 mm
UB4N273M16	599260	Steel	Electrogalvanized	273 mm	250	M16	331 mm
UB4N323M10	599343	Steel	Electrogalvanized	323 mm	300	M10	389 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

