

# EuropacPRO 19" Subrack Kit for DIN Connector, Retrofit Shielding

Non-shielded subrack for Din Connector mounting EN 60603-2 (DIN 41612).



## FEATURES

Subrack with side panel type F ("flexible"), front 19" bracket included, depth-adjustable 19" bracket sold separately (not included in items delivered)

Aluminum construction

IP 20, in accordance with IEC 60529

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Rear horizontal rails for connector mounting (IEC 60603-2 / DIN 41612)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Horizontal rail type "light"

|                       |                      |
|-----------------------|----------------------|
| <b>EMC Shielding:</b> | No                   |
| <b>Finish:</b>        | Anodized; Passivated |
| <b>Material:</b>      | Aluminum             |
| <b>Product Type:</b>  | Subrack/Chassis      |



## SPECIFICATIONS

Table 1/2

| Catalog Number | Rack Height | Depth | Package Quantity | For Mounting  | Board Depth                | Gasket Type                         |
|----------------|-------------|-------|------------------|---------------|----------------------------|-------------------------------------|
| 24563-191      | 3U          | 175mm | 1                | DIN Connector | 160mm                      | Stainless Steel EMC (retrofittable) |
| 24563-192      | 3U          | 235mm | 1                | DIN Connector | 160mm, 220mm               | Stainless Steel EMC (retrofittable) |
| 24563-193      | 3U          | 295mm | 1                | DIN Connector | 160mm, 220mm, 280mm        | Stainless Steel EMC (retrofittable) |
| 24563-194      | 3U          | 355mm | 1                | DIN Connector | 160mm, 220mm, 280mm, 340mm | Stainless Steel EMC (retrofittable) |
| 24563-491      | 6U          | 175mm | 1                | DIN Connector | 160mm                      | Stainless Steel EMC (retrofittable) |
| 24563-492      | 6U          | 235mm | 1                | DIN Connector | 160mm, 220mm               | Stainless Steel EMC (retrofittable) |
| 24563-493      | 6U          | 295mm | 1                | DIN Connector | 160mm, 220mm, 280mm        | Stainless Steel EMC (retrofittable) |
| 24563-494      | 6U          | 355mm | 1                | DIN Connector | 160mm, 220mm, 280mm, 340mm | Stainless Steel EMC (retrofittable) |

Table 2/2

| Catalog Number | Handle Included | Mounting | Complies With   | Rack Width | Static Load |
|----------------|-----------------|----------|-----------------|------------|-------------|
| 24563-191      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        |
| 24563-192      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        |
| 24563-193      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        |
| 24563-194      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        |
| 24563-491      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        |
| 24563-492      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        |
| 24563-493      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        |
| 24563-494      | No              | Rack     | IEC 60297-3-103 | 84HP       | 11kg        |

## ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

