


Speedway Cable Ladder Equal Tee



FEATURES

- Creates a quick and easy equal tee pathway intersection
- Provides optimal support for high-performance low voltage and data cables
- Innovative SPEEDLOK integrated coupling system
- Safety edge protects cables during installation
- Slotted side channel, eliminating field drilling for cut-to-length applications
- IEC 61537 load rating and earthing compliant
- Responsive design and layout services, including seismic

Material: Steel
Finish: Hot-Dip Galvanized



SPECIFICATIONS

Table 1/2


Catalog Number	Article Number	Width (W)	Angle (a)	A	B	C
CL110X150ETHD	840700	150 mm	90 °	900 mm	450 mm	950 mm
CL110X300ETHD	840710	300 mm	90 °	900 mm	525 mm	950 mm
CL110X450ETHD	840720	450 mm	90 °	900 mm	600 mm	950 mm
CL110X600ETHD	840730	600 mm	90 °	900 mm	675 mm	950 mm
CL110X750ETHD	840740	750 mm	90 °	900 mm	750 mm	950 mm
CL110X900ETHD	840750	900 mm	90 °	900 mm	825 mm	950 mm

Table 2/2

Catalog Number	Article Number	D	E
CL110X150ETHD	840700	80 mm	110 mm
CL110X300ETHD	840710	80 mm	110 mm
CL110X450ETHD	840720	80 mm	110 mm
CL110X600ETHD	840730	80 mm	110 mm

Catalog Number	Article Number	D	E
CL110X750ETHD	840740	80 mm	110 mm
CL110X900ETHD	840750	80 mm	110 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America
+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe
Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe
Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC
Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

