

115M Standard Duty Loop Hanger



The 115M Standard Duty Loop Hanger is ideal for suspending stationary, non-insulated pipe lines, including CPVC pipes, in fire sprinkler systems. A knurled insert nut helps simplify vertical adjustments and flared edges on the base (1/2" to 4" sizes) help protect pipes from coming into contact with any sharp edges of the hanger.

FEATURES

Flared edges help prevent any sharp surfaces from coming into contact with the pipe (1/2" to 4" sizes)

Retained insert nut helps ensure the loop hanger and insert nut stay together

Recommended for the suspension of stationary non-insulated pipe lines

Manufactured to use the minimum rod size permitted by NFPA® for fire sprinkler piping

Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

Material: Steel
Finish: Pregalvanized



SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	Rod Size (RS)	A	B
115M0050EG	597860	15	21.3 mm	M10	71 mm	28.6 mm
115M0075EG	597870	20	26.9 mm	M10	75.9 mm	30.2 mm
115M0100EG	597880	25	33.7 mm	M10	82.5 mm	34.9 mm
115M0125EG	597890	32	42.4 mm	M10	90.6 mm	38.1 mm
115M0150EG	597900	40	48.3 mm	M10	96.7 mm	41.3 mm
115M0200EG	597910	50	60.3 mm	M10	108.6 mm	47.6 mm
115M0250EG	597920	65	76 mm	M10	150.8 mm	87.3 mm
115M0300EG	597930	80	89 mm	M10	166.3 mm	88.2 mm
115M0400EG	597940	100	114 mm	M10	192.5 mm	100.9 mm

Catalog Number	Article Number	NB/DN	Outer Diameter (OD)	Rod Size (RS)	A	B
115M0500EG	597950	125	140 mm	M12	232.7 mm	120 mm
115M0600EG	597960	150	165 mm	M12	286.6 mm	160.4 mm
115M0800EG	597970	200	219 mm	M12	327.1 mm	175.1 mm

Table 2/2

Catalog Number	Article Number	C	Ultimate Static Load (F)	Certifications
115M0050EG	597860	25.4 mm	5000N	cUL, UL, ITB
115M0075EG	597870	23.9 mm	5000N	cUL, UL, FM Approved, Pipe Hanger Components, ITB
115M0100EG	597880	24.1 mm	5000N	cUL, UL, FM Approved, Pipe Hanger Components, ITB
115M0125EG	597890	24.1 mm	5000N	ITB, cUL, FM Approved, Pipe Hanger Components, UL
115M0150EG	597900	24.1 mm	5000N	ITB, cUL, FM Approved, Pipe Hanger Components, UL
115M0200EG	597910	23.9 mm	5000N	cUL, UL, ITB, FM Approved, Pipe Hanger Components
115M0250EG	597920	50.8 mm	14000N	FM Approved, Pipe Hanger Components, cUL, ITB, UL
115M0300EG	597930	49.7 mm	14000N	FM Approved, Pipe Hanger Components, cUL, ITB, UL
115M0400EG	597940	48.9 mm	14000N	ITB, cUL, UL, FM Approved, Pipe Hanger Components
115M0500EG	597950	57.1 mm	20000N	ITB, UL, cUL, FM Approved, Pipe Hanger Components
115M0600EG	597960	84.1 mm	20000N	UL, FM Approved, Pipe Hanger Components, ITB, cUL
115M0800EG	597970	73.4 mm	20000N	cUL, UL, FM Approved, Pipe Hanger Components, ITB



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

