


# Cantilever Arm with E4 Channel

## FEATURES

Perforated, cold rolled

Slotted backplate



**Material:** Steel  
**Finish:** Electrogalvanized



## SPECIFICATIONS

| Catalog Number | Article Number | Length (L) |
|----------------|----------------|------------|
| CE420H0200EG   | 599935         | 200mm      |
| CE420H0300EG   | 599950         | 300mm      |
| CE420H0350EG   | 599960         | 350mm      |
| CE420H0450EG   | 599970         | 450mm      |
| CE420H0550EG   | 599980         | 550mm      |
| CE420H0650EG   | 599990         | 650mm      |
| CE420H0800EG   | 599995         | 800mm      |

**Height (H):** 120 mm

**Width (W):** 40 mm

**Thickness (T):** 2 mm

**A:** 40 mm


**B:** 38 mm

**C:** 15.5 mm

**D:** 50 mm

**E:** 6 mm  
**X:** 11 x 18 mm  
**Y:** 14 x 27 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

|                                                                                                     |                                                                                |                                                                                |                                                                                |
|-----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------|
| <b>North America</b><br>+1.800.753.9221<br>Option 1 – Customer Care<br>Option 2 – Technical Support | <b>Europe</b><br>Netherlands:<br>+31 800-0200135<br>France:<br>+33 800 901 793 | <b>Europe</b><br>Germany:<br>800 1890272<br>Other Countries:<br>+31 13 5835404 | <b>APAC</b><br>Shanghai:<br>+ 86 21 2412 1618/19<br>Sydney:<br>+61 2 9751 8500 |
|-----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------|--------------------------------------------------------------------------------|

