

PEMSA Wire Basket Tray Splice Bar, Black

CATALOG NUMBER

WBTSPBAR300BG

FEATURES

Added mechanical splice strength

Works with wide range of tray sizes and configurations

IEC 61537 load rating and earthing compliant



PRODUCT ATTRIBUTES

Article Number: 820703

Material: Steel

Finish: Electrogalvanized


Color: Black

Length (L): 300mm

Width (W): 22 mm

Thickness (T): 1.5 mm

Slot Size (SS): 7 x 28 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

