

H-Ti/T Rod to Flange Clip



FEATURES

Suspends threaded rod from beam flanges

Threaded rod hanger can swivel to provide a vertical dropdown

Requires only a hammer to install

Material: Spring Steel
Finish: nVent CADDY Armour




SPECIFICATIONS

Catalog Number	Article Number	Hole Size (HS)	Hole Type	Flange Thickness (FT)	Static Load	Certifications
160000	160000	11 mm	Plain	2 - 3 mm	700N	ITB
160010	160010	11 mm	Plain	3 - 8 mm	900N	ITB
160030	160030	11 mm	Plain	14 - 20 mm	900N	ITB
M10TI24	175000	10 mm	Threaded	3 - 8 mm	900N	ITB
M10TI58	175010	10 mm	Threaded	8 - 14 mm	900N	ITB
M10TI912	175020	10 mm	Threaded	14 - 20 mm	900N	ITB
M6TI24	174820	6 mm	Threaded	3 - 8 mm	900N	ITB, CE, 4QTI24, 4QTI58, M6TI24, M6TI58
M6TI24R5	191024	6 mm	Threaded	3 - 8 mm	900N	

Catalog Number	Article Number	Hole Size (HS)	Hole Type	Flange Thickness (FT)	Static Load	Certifications
M6TI4	174810	6 mm	Threaded	2 - 3 mm	700N	ITB
M6TI58	174830	6 mm	Threaded	8 - 14 mm	900N	ITB, CE, 4QTI24, 4QTI58, M6TI24, M6TI58
M6TI912	174840	6 mm	Threaded	14 - 20 mm	900N	ITB
M8TI24	174910	8 mm	Threaded	3 - 8 mm	900N	ITB
M8TI4	174900	8 mm	Threaded	2 - 3 mm	700N	ITB
M8TI58	174920	8 mm	Threaded	8 - 14 mm	900N	ITB
M8TI912	174930	8 mm	Threaded	14 - 20 mm	900N	ITB
T1058	160020	11 mm	Plain	8 - 14 mm	900N	ITB

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

