

# Single Cable Bracket with Plug, 10 mm Max dia

## CATALOG NUMBER

**SCKB10**



## FEATURES

Ideal for smaller runs of cables

Up to two plastic conduit clips can be attached to the bracket allowing the support of cables and conduits using a single hole in the concrete

Flexible clip retains shape and allows for cables to be inserted after installation

Cables are neatly installed providing a consistent and professional appearance

Low profile allows for installations in tight spaces

Tool-free push-in installation after hole has been drilled into the concrete

Halogen free

UV-stabilized

## PRODUCT ATTRIBUTES

Article Number: 800040

Material: Polypropylene

Temperature: -10 to 85 °C

Cable Capacity: 13

Drill Hole Diameter: 6mm

Drill Hole Depth: 30mm


Height (H): 48 mm

Length (L): 149mm

Width (W): 15 mm

Static Load: 240N

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com](http://nVent.com)

