

PBF Two Hole Base Plate for Threaded Pipe

FEATURES

Medium duty with two holes and one nut/adaptor



Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS


Table 1/2

Catalog Number	Article Number	Gewinde (G)	Length (L)	Width (W)	Thickness (T)	A
PBT050L120	587120	1/2"	120mm	40 mm	4 mm	81 mm
PBT050L80	587125	1/2"	80mm	30 mm	3 mm	50 mm

Table 2/2

Catalog Number	Article Number	B	C
PBT050L120	587120	18 mm	11 mm
PBT050L80	587125	18 mm	9 mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

