

PEMSA Wire Basket Tray L Bracket



FEATURES

Easy to use, quick connect feature

Ideal for typical wall and channel installations



IEC 61537 load rating and earthing compliant

Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	Article Number	Length (L)	Width (W)	Height (H)	Static Load	Certifications
WBT100LBRKT	820200	170mm	54 mm	138 mm	588N	ANOR EU WTB B S, DoP, CADDY EU WBT, CE, CADDY EU WBT BRT
WBT150LBRKT	820210	220mm	54 mm	138 mm	588N	CE, CADDY EU WBT BRT, DoP, CADDY EU WBT, ANOR EU WTB B S
WBT200LBRKT	820220	270mm	54 mm	138 mm	588N	
WBT300LBRKT	820230	370mm	54 mm	138 mm	373N	UKCA, CADDY EU WBT B, DoP, CADDY EU WBT, ANOR EU WTB B S, CE, CADDY EU WBT BRT
WBT400LBRKT	820240	470mm	54 mm	138 mm	275N	ANOR EU WTB B S, DoP, CADDY EU WBT, UKCA, CADDY EU WBT B, CE, CADDY EU WBT BRT



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

