


Terminal Enclosure Mild Steel, STE



Rated IP66, the nVent HOFFMAN portfolio mild steel terminal enclosure range, STE, is available off the shelf in many different sizes. The mild steel enclosures are well suited for demanding indoor environments. The IP66 rating means water and dust are prevented from entering the enclosure, keeping electrical equipment and components inside safe and avoiding failure and unnecessary downtime. The slim design of the enclosure helps save space, while the 180° door hinge offers easy access for operators and routine maintenance needs. The enclosures also include a standard lock for security.

FEATURES

Material: 1.2 mm mild steel.

Body: Folded and seam welded. Four 8.5 mm diameter holes for wall fixation. Four M6×13 studs for bottom profiles/mounting plate fixation.

Door: With durable 180 degree Zamak hinges, the easy-to-install door can be mounted for left or right hand opening. An injected polyurethane gasket provides a secure seal.

Gasket: Injected polyurethane gasket.

Lock: nVent HOFFMAN portfolio customized Zamak double-bit 3 mm lock, with 90 degree movement and an anti vibration mechanism.

Earthing: M8x18 mm earthing studs in body and cover, M8 nuts, earthing washers and earthing labels.

Finish: RAL 7035, structured powder coating.

Delivery: Body, door, hinge, lock, plastic double-bit 3 mm key and mounting accessories.

The mounting plate (BMP), DIN profiles (BDR) and mounted on profiles (BPP) must be ordered separately in order to complete the installation.

Material:	Mild Steel
Finish:	Powder Coated
Color:	Light Gray
Color Code:	RAL 7035

SPECIFICATIONS

Catalog Number	Height	Width	Depth	Thickness
STE151508	150mm	150mm	80mm	1.2mm
STE151512	150mm	150mm	120mm	1.2mm
STE202008	200mm	200mm	80mm	1.2mm
STE202012	200mm	200mm	120mm	1.2mm
STE203012	200mm	300mm	120mm	1.2mm
STE301508	150mm	300mm	80mm	1.2mm
STE301512	150mm	300mm	120mm	1.2mm
STE302008	200mm	300mm	80mm	1.2mm
STE302012	300mm	200mm	120mm	1.2mm
STE303012	300mm	300mm	120mm	1.2mm
STE402008	200mm	400mm	80mm	1.2mm
STE402012	200mm	400mm	120mm	1.2mm
STE403012	300mm	400mm	120mm	1.2mm
STE404012	400mm	400mm	120mm	1.2mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.