

BC10 Beam Clamp with BC15 Swivel

FEATURES

Swivel attachment suitable for sloped beams



SPECIFICATIONS

Table 1/2


Catalog Number	Material	Finish	Rod Size (RS)	Flange Thickness (FT)	A	Screw Diameter (Sc)
BC101500EG	Steel	Electrogalvanized	0.375, 0.5	19.1 mm Max	25.4 mm	10

Table 2/2

Catalog Number	Torque (TQ)	Static Load
BC101500EG	6.78 N·m	2225N

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

